









技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

序号	品名	材质
①	0.5 Pitch C型 单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型 单槽立式BTB公座端子	铜合金/表面点镀金

REV.	ECN NO OR DESCRIPTION	REVISED	DATE
合高(H)	公座单高	母座单高	
1.5	1.3	1.4	
2.0	1.3	1.9	
2.5	1.3	2.4	

Part No	CKT	A	B	C
BTM0513-10PDLWR-GO	2X5	2.00	3.40	5.50
BTM0513-12PDLWR-GO	2X6	2.50	3.90	6.00
BTM0513-14PDLWR-GO	2X7	3.00	4.40	6.50
BTM0513-16PDLWR-GO	2X8	3.50	4.90	7.00
BTM0513-18PDLWR-GO	2X9	4.00	5.40	7.50
BTM0513-20PDLWR-GO	2X10	4.50	5.90	8.00
BTM0513-22PDLWR-GO	2X11	5.00	6.40	8.50
BTM0513-24PDLWR-GO	2X12	5.50	6.90	9.00
BTM0513-26PDLWR-GO	2X13	6.00	7.40	9.50
BTM0513-28PDLWR-GO	2X14	6.50	7.90	10.00
BTM0513-30PDLWR-GO	2X15	7.00	8.40	10.50
BTM0513-32PDLWR-GO	2X16	7.50	8.90	11.00
BTM0513-34PDLWR-GO	2X17	8.00	9.40	11.50
BTM0513-36PDLWR-GO	2X18	8.50	9.90	12.00
BTM0513-38PDLWR-GO	2X19	9.00	10.40	12.50
BTM0513-40PDLWR-GO	2X20	9.50	10.90	13.00
.....	...	...	...	...
BTM0513-100PDLWR-GO	2X50	24.50	25.90	28.00

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10

东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD				
TITLE	0.5 Pitch C型单槽立式BTB公座业务图(单高1.3)			
DWN	xiong	PART NO.	BTM0513-XXPDLWR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4
CUSTOMER COPY				