









P.C.B LAYOUT



SECT B-B



SPECIFICATION:

- 1.MATERIAL:

- 1.1 HOUSING: LCP 30% G/F UL 94V-0

- 1.2 COLOR:BLACK

- 1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

- 1.4 PEG: BRASS C2680R-H,T=0.30mm

- 2.FINISH:

- 2.1 CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

- ## 2.2 100u" TIN PLATING ON SOLDERTAILS

- ### 2.3 30u" NICKEL UNDERPLATING OVER ALL

- ## 2.4 PEG:100u" TIN PLATING ON SOLDERTAILS

- 2.5 30u" NICKEL UNDERPLATING OVER ALL

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

环境要求		产品必须符合ROHS要求			
3	Peg	Brass C2680R		Tin/Ni Plated	
2	Terminal	Pho.Bronze C5191		Gold/Tin Plated	
1	Housing	High Temp		Black UL 94V-0	
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK	
UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD			
DECIMALS: ANGLES:		TITLE	SATA 7+15P 母座单排直立式180°(欧置款)		
X	±0.30	X	±2°	DWN xiong PART NO. SATA-030F-22PS1BY	
X.X	±0.20	X.X	±1°	CHKD lee SCALE:1:1	UNIT: mm
X.XX	±0.10	APVD wang	SIZE: A4	SHEET:1OF 1	REV: A4
CUSTOMER COPY					