

SPECIFICATION:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:






2.1 CONTACT: 1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDERTAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDERTAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



REV.	ECN NO OR DESCRIPTION	REVISED	DATE

环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS:		ANGLES:	
X	: ± 0.30	X	: $\pm 2^\circ$
X.X	: ± 0.20	X.X	: $\pm 1^\circ$
X.XX	: ± 0.10		



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7+15P 母座板上6.74 SMT侧插式			
DWN	xiong	PART NO. SATA-033F-22PS1BY		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY