



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:

2.1 CONTACT:1u"3u"5u"15u" GOLD PLATING ON CONTACT AREA









2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL

ITEM	DIM A	形状	DIM B
SATA-027FB-22PS1BY	2.10		2.08
SATA-027F-22PS1BY	2.30		

RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE: ±0.05

环境要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R-H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

UNLESS OTHERWISE
SPECIFIED TOLERANCESDECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	SATA 7+15P 母座SMT H3.50 板上侧插式			
DWN	xiong	PART NO.	SATA-027F-22PS1BY	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY