











5		6		7		8	
REV	ECN	DESCRIPTION			MDF' D	DATE	
1.0	/	新发行			fan Z. J.	2026-06-01	

Electrical:

- 1.Voltage: 50V AC(rms)/DC;
- 2.Current: 0.5A AC(rms)/DC;
- 3.Contact Resistance: 40 mΩ Max(initial);
- 4.Dielectric Withstanding Voltage: 200 V AC/rms;
- 5.Insulation Resistance: 500 MΩ Min;
- 6.Operating Temp: -55° C ~+85° C

Material:

- 1.Housing: Lcp Natuer (UL94V-0)
- 2.Terminal: Phosphor Bronze C5191 R-H.



Contacts	A	B	C	D	E	F	G	H
26	11.5	08.3	07.0	06.0	08.5	11.3	3.5	3.0
30	12.5	09.3	08.0	07.0	09.5	12.3		
60	20.0	16.8	15.5	14.5	17.0	19.8		
70	22.5	19.3	18.0	17.0	19.5	22.3		
80	25.0	21.8	20.5	19.5	22.0	24.8		

.X ±0.20	.X° ±1.0°
.XX ±0.10	.XX° ±0.5°
.XXX ±0.05	.XXX° ±0.2°
	SCALE 1:1 UNIT mm
PAGE: 1/1	REV: 1.0

JMECONN 深圳市文章济美科技有限公司 SHENZHEN WENZHANG JIMEI TECHNOLOGY CO., LTD	
Part Name: DF17 0.5P BTB 带接地片 H3.0母座	Approved:
Part No.: 5001-DF170535-70FR-00-B	Checked:
Title:	Material:
Drawing No.: G8BTC0035	Date: 2026-06-01