






REV.	ECN NO OR DESCRIPTION	REVISED	DATE



规格说明: Specifications:
电气特性: Electrical:
1. 额定电流: Current Rating 3A/contact terminal
2. 额定电压: Voltage Rating 30V DC
3. 接触阻抗: Contact Resistance 30 milliohms MAX
4. 耐压: Dielectric Withstanding Voltage: 500 V AC AT Sea Level
5. 绝缘阻抗: Insulation Resistance 1000 MEGA ohms MIN
物理性能: Mechanical:
1. 插拔力: Connector Mate and Unmate Force
Mate force: 3.57kgf(MAX) Unmate force: 1.02kgf(MIN)
原材料: Material:
1. 塑胶: Housing: LCP/PBT
Hing Temperature Thermoplastics,
2. 端子: Contact: Copper Alloy C2680
3. 外壳: Shell: Copper Alloy C2680/SPCC
电镀: Finish:
1. 端子: Contact: Plated Gold in Mating Area;
Tin On Solder Tails
端子四周镀 30-50U”(MIN) 镍, 接触点镀金 0.5-0.8U”
2. 外壳: Shell: 四周镀 (MIN) 镍 50-80U”
Nickel Plating

UNLESS OTHERWISE SPECIFIED TOLERANCES				东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE	USB2.0直插15.1直边直脚			
X :±0.30	X :±2°	DWN	xiong	PART NO. USB-UD250-BWS		
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE: 1: 1	UNIT: mm	
X.XX :±0.10		APVD	wang	SIZE: A4	SHEET: 10F 1	REV: A4
CUSTOMER COPY						