









REV.	ECN NO OR DESCRIPTION	REVISED	DATE



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.03\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$



序号	品名	材质
①	0.5 Pitch D型 单槽侧插BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.5 Pitch D型 单槽侧插BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
BTM0533-4PDLYR-GO	2*2	0.50	2.50	2.50	1.70
BTM0533-6PDLYR-GO	2*3	1.00	3.00	3.00	2.20
BTM0533-8PDLYR-GO	2*4	1.50	3.50	3.50	2.70
BTM0533-10PDLYR-GO	2*5	2.00	4.00	4.00	3.20
BTM0533-12PDLYR-GO	2*6	2.50	4.50	4.50	3.70
BTM0533-14PDLYR-GO	2*7	3.00	5.00	5.00	4.20
BTM0533-16PDLYR-GO	2*8	3.50	5.50	5.50	4.70
BTM0533-18PDLYR-GO	2*9	4.00	6.00	6.00	5.20
BTM0533-20PDLYR-GO	2*10	4.50	6.50	6.50	5.70
BTM0533-22PDLYR-GO	2*11	5.00	7.00	7.00	6.20
BTM0533-24PDLYR-GO	2*12	5.50	7.50	7.50	6.70
BTM0533-26PDLYR-GO	2*13	6.00	8.00	8.00	7.20
BTM0533-28PDLYR-GO	2*14	6.50	8.50	8.50	7.70
BTM0533-30PDLYR-GO	2*15	7.00	9.00	9.00	8.20
BTM0533-32PDLYR-GO	2*16	7.50	9.50	9.50	8.70
BTM0533-34PDLYR-GO	2*17	8.00	10.00	10.00	9.20
BTM0533-36PDLYR-GO	2*18	8.50	10.50	10.50	9.70
BTM0533-38PDLYR-GO	2*19	9.00	11.00	11.00	10.20
BTM0533-40PDLYR-GO	2*20	9.50	11.50	11.50	10.70
.....	...	...	...	...	...
BTM0533-80PDLYR-GO	2*40	19.50	21.50	21.50	20.70

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X : ±0.30 X : ±2°
X.X : ±0.20 X.X : ±1°
X.XX : ±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.5 Pitch D型单槽侧插BTB公座业务图(单高3.3)			
DWN	xiong	PART NO.BTM0533-XXPDLYR-GO		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY