





技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 125V, AC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ

序号	品名	材质
①	0.8 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0, 颜色: 黑色
②	0.8 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0, 颜色: 黑色

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

High photosynthesis 合高(H)	The female seat neight 母座高度(H1)	The male seat neight 公座高度(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9

Part No	CKT	A	B	C	D	E
BTF0845-8PSLYR-GO	8	2.40	3.50	5.10	4.20	4.00
BTF0845-10PSLYR-GO	10	3.20	4.30	5.90	5.00	
BTF0845-12PSLYR-GO	12	4.00	5.10	6.70	5.80	
BTF0845-14PSLYR-GO	14	4.80	5.90	7.50	6.60	
BTF0845-16PSLYR-GO	16	5.60	6.70	8.30	7.40	
BTF0845-18PSLYR-GO	18	6.40	7.50	9.10	8.20	
BTF0845-20PSLYR-GO	20	7.20	8.30	9.90	9.00	8.00
BTF0845-22PSLYR-GO	22	8.00	9.10	10.70	9.80	
BTF0845-24PSLYR-GO	24	8.80	9.90	11.50	10.60	
BTF0845-26PSLYR-GO	26	9.60	10.70	12.30	11.40	
BTF0845-28PSLYR-GO	28	10.40	11.50	13.10	12.20	
BTF0845-30PSLYR-GO	30	11.20	12.30	13.90	13.00	
BTF0845-32PSLYR-GO	32	12.00	13.10	14.70	13.80	
BTF0845-34PSLYR-GO	34	12.80	13.90	15.50	14.60	
BTF0845-36PSLYR-GO	36	13.6	14.70	16.30	15.40	
BTF0845-38PSLYR-GO	38	14.40	15.50	17.10	16.20	
BTF0845-40PSLYR-GO	40	15.20	16.30	17.90	17.00	
BTF0845-44PSLYR-GO	44	16.80	17.90	19.50	18.60	
BTF0845-50PSLYR-GO	50	19.20	20.30	21.90	21.00	
BTF0845-60PSLYR-GO	60	23.20	24.30	25.90	25.00	
BTF0845-70PSLYR-GO	70	27.20	28.30	29.90	29.00	
BTF0845-80PSLYR-GO	80	31.20	32.30	33.90	33.00	
BTF0845-100PSLYR-GO	100	39.20	40.30	41.90	41.00	

UNLESS OTHERWISE SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.8 Pitch双槽立式BTB母座业务图(单高4.5)			
DWN	xiong	PART NO.	BTF0845-XXPSLYR-GO	
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:1OF 1	REV: A4

CUSTOMER COPY