






SEC:A-A



SEC:B-B



SEC:C-C



PCB LAYOUT

技术指标(Technical Index):

- 1.工作温度(Temperature range):-25°C~+85°C.
- 2.额定电压(Rated voltage):250V DC/AC.
- 3.额定电流(Rated current):2.0A DC/AC.
- 4.接触电阻(Contact resistance):≤20mΩ.
- 5.耐压值(Dielectricwithstanding voltage):1000V AC/minute.
- 6.绝缘电阻(Insulation resistance):≥1000MΩ.
- 7.适用线规(Apply to gauge):AWG#24~#28.
- 8.适用基板厚度(Applicable PC board thickness):1.2~1.6mm.

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

MANUFACTURE DWG		东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES		TITLE: SAN2.0 WTB直插板端子	
DECIMALS:	ANGLES:	PAR	WAFER-SAN2.0-DZ
X.:±0.50	±1°	DWN	Lucas
X.X:±0.20		CHKD	Ethan
X.XX:±0.10		APVD	Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	SHEET:1F1
			REV:A