






Kinghelm®

Rev	描述 Description	变更编号 Change number	日期 Date
A	First issue	---	2023/06/07



Front View



Rear View

Recommended Mounting Hole	Pin height

Pin Assignments Front View				
3Pin	3Pin	5Pin	6Pin	8Pin

The View				深圳市金航标电子有限公司	
单位 unit mm		页码 page 1/1		SHENZHEN KINGHELM ELECTRON CO.,LTD.	
图号 Drawing NO		料号 Part Number KH-869MCS0281-XP		产品名称 Circular Panel Mount, Male, M8	
文件保密 File security This drawing shall not be copied, circulated or used for other purposes without permission. 本图纸未经许可, 不可复制、外传或它用		未注公差 Unmarked tolerance		绘图 Draw drawing	Huang guanhui
		零部件 Parts X. ±0.5 X.X ±0.20 X.XX ±0.10	线性 Line ≤10 ±1 10~50 ±1.5 >50 ±4%	审核 Check	FuLiu
		角度 angle ±3°		客户确认 Customer confirmation	

NOTES:

- Rated voltage/current: 3pin: 60V/3A
4pin: 60V/3A
5pin: 60V/3A
6, 8pin: 30V/1A
- Withstanding voltage: 3, 4pin: AC850V/1 Min .
5, 6, 8pin: AC650V/1 Min
- Levels of protection: IP67
- Connection mode: Soldering
- Operating temperature: -20℃~+85℃
- RoHS Compliance

5	Contacts	Brass	Gold	3-8PCS
4	O-Ring	Rubber	/	1PCS
3	Nut M8*1	Brass	Nickel	1PCS
2	Body	Brass	Nickel	1PCS
1	Insulator	PA66	Black	1PCS
No.	描述 Description	材质 Material	材质 Finish	数量 Qty/Unit