




技术指标:

- | High photosynthesis
合高 (H) | The female seat
neight 母座半高 (H1) | The male
seat neight 公座半高 (H2) | Insertion height
(H3) |
|-------------------------------|-------------------------------------|-----------------------------------|--------------------------|
| 3.00 | 2.20 | 0.80 | 1.60 |
| 3.50 | 2.20 | 1.30 | 1.60 |
| 4.00 | 3.00 | 1.00 | 1.90 |
| 4.50 | 3.50 | 1.00 | 1.90 |
| 5.00 | 4.00 | 1.00 | 1.90 |
| 5.50 | 4.50 | 1.00 | 1.90 |
| 6.00 | 4.00 | 2.00 | 1.90 |
| 6.50 | 4.50 | 2.00 | 1.90 |
| 7.00 | 3.00 | 4.00 | 1.90 |
| 7.50 | 3.50 | 4.00 | 1.90 |
| 8.00 | 4.00 | 4.00 | 1.90 |
| 8.50 | 4.50 | 4.00 | 1.90 |



UNLESS OTHERWISE
SPECIFIED TOLERANCES



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

DECIMALS:		ANGLES:	
X	: ± 0.30	X	: $\pm 2^\circ$
X.X	: ± 0.20	X.X	: $\pm 1^\circ$
X.XX	: ± 0.10		

TITLE	0.5 Pitch双槽立式BTB号(单高3.5)			
DWN	xiong	PART NO. BTF0535-XXPSLYR-GO		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY



PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
BTF0535-8PSLYR-GO	8	1.50	2.55	4.70	3.40	4.00
BTF0535-10PSLYR-GO	10	2.00	3.05	5.20	3.90	
BTF0535-12PSLYR-GO	12	2.50	3.55	5.70	4.40	
BTF0535-14PSLYR-GO	14	3.00	4.05	6.20	4.90	
BTF0535-16PSLYR-GO	16	3.50	4.55	6.70	5.40	
BTF0535-18PSLYR-GO	18	4.00	5.05	7.20	5.90	
BTF0535-20PSLYR-GO	20	4.50	5.55	7.70	6.40	
BTF0535-22PSLYR-GO	22	5.00	6.05	8.20	6.90	
BTF0535-24PSLYR-GO	24	5.50	6.55	8.70	7.40	
BTF0535-26PSLYR-GO	26	6.00	7.05	9.20	7.90	
BTF0535-28PSLYR-GO	28	6.50	7.55	9.70	8.40	8.00
BTF0535-30PSLYR-GO	30	7.00	8.05	10.20	8.90	
BTF0535-32PSLYR-GO	32	7.50	8.55	10.70	9.40	
BTF0535-34PSLYR-GO	34	8.00	9.05	11.20	9.90	
BTF0535-36PSLYR-GO	36	8.50	9.55	11.70	10.40	
BTF0535-38PSLYR-GO	38	9.00	10.05	12.20	10.90	
BTF0535-40PSLYR-GO	40	9.50	10.55	12.70	11.40	
BTF0535-44PSLYR-GO	44	10.50	11.05	13.70	12.40	
BTF0535-50PSLYR-GO	50	12.00	13.05	15.20	13.90	
BTF0535-60PSLYR-GO	60	14.50	15.55	17.70	16.40	
BTF0535-70PSLYR-GO	70	17.00	18.05	20.20	18.90	
BTF0535-80PSLYR-GO	80	19.50	20.55	22.70	21.40	
BTF0535-100PSLYR-GO	100	24.50	25.55	27.70	26.40	

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

UNLESS OTHERWISE
SPECIFIED TOLERANCES

DECIMALS: ANGLES:
X :±0.30 X :±2°
X.X :±0.20 X.X :±1°
X.XX :±0.10



东莞市汉博电子科技有限公司
DONGGUAN HANBO TECHNOLOGY CO., LTD

TITLE	0.5 Pitch 双槽立式BTB等(单高3.5)			
DWN	xiong	PART NO BTF0535-XXPSLYR-GO		
CHKD	lee	SCALE:1:1	UNIT: mm	
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4

CUSTOMER COPY