









SECT B-B



SECT C-C



P.C.B LAYOUT

SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP 30%G/F UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

2.FINISH:

2.1 CONTACT: 1u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

REV.	ECN NO OR DESCRIPTION	REVISED	DATE

环境要求		产品必须符合ROHS要求		
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
UNLESS OTHERWISE SPECIFIED TOLERANCES		 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD		
DECIMALS: ANGLES:		TITLE SATA 7+15P 单排脚B脚位中间扣板1.0(PIN0.25)平口		
X :±0.30	X :±2°	DWN	xiong PART NO. SATA-031F-22PS1BY	
X.X :±0.20	X.X :±1°	CHKD	lee	SCALE:1:1 UNIT: mm 
X.XX :±0.10		APVD	wang	SIZE: A4 SHEET:10F 1 REV: A4
CUSTOMER COPY				