





SEC:A-A




SEC:B-B



SEC:C-C

技术指标(Technical Index):

- 1.工作温度(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):50V DC/AC(rms).
- 3.额定电流(Rated current):0.7A(DC/AC).
- 4.耐压值(Dielectricwithstanding voltage):500V AC/minute.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.适用线规(Apply to gauge):AWG#26~#30.
- 7.适用基板厚度(Applicable PC board thickness):1.2~1.6mm.



PCB LAYOUT

序号	品名	材质
1	端子	Phosphor Bronze Bright tin plated

MANUFACTURE DWG		 东莞市讯普电子科技有限公司 DongGuan XunPu Electronics Co.,Ltd	
UNLESS OTHERWISE SPECIFIED TOLERANCES			TITLE: SZN1.5 WTB直插板端子
DECIMALS:	ANGLES:		PAR WAFER-SZN1.5-DZ
X.:±0.30	X.':±5°		DWN Lucas
X.X:±0.20	X.X':±3°		CHKD Ethan
X.XX:±0.10	X.XX':±2°		APVD Jacob
CUSTOMER COPY		SCALE:1:1	UNIT:MM
		SIZE:A4	UNIT:MM
		SHEET:1F1	REV:A