









REV.		ECN NO OR DESCRIPTION		REVISED	DATE
		合高(H)	公座单高	母座单高	
		1.5	1.3	1.4	
		2.0	1.3	1.9	
		2.5	1.3	2.4	
CKT	A	B		C	
2X5	2.00	3.40		5.50	
2X6	2.50	3.90		6.00	
2X7	3.00	4.40		6.50	
2X8	3.50	4.90		7.00	
2X9	4.00	5.40		7.50	
2X10	4.50	5.90		8.00	
2X11	5.00	6.40		8.50	
2X12	5.50	6.90		9.00	
2X13	6.00	7.40		9.50	
2X14	6.50	7.90		10.00	
2X15	7.00	8.40		10.50	
2X16	7.50	8.90		11.00	
2X17	8.00	9.40		11.50	
2X18	8.50	9.90		12.00	
2X19	9.00	10.40		12.50	
2X20	9.50	10.90		13.00	
...	...	...		...	
2X50	24.50	25.90		28.00	
 东莞市汉博电子科技有限公司 DONGGUAN HANBO TECHNOLOGY CO., LTD					
TITLE 0.5 Pitch C型单槽立式BTB母座芯(单高2.4)					
DWN	xiong	PART NO. BTF0524-XXPDLWR-GO			
CHKD	lee	SCALE:1:1	UNIT: mm		
APVD	wang	SIZE: A4	SHEET:10F 1	REV: A4	
CUSTOMER COPY					



技术指标:

- 1.塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
- 2.温度范围:-40°C~85°C.
- 3.额定电压:50V,AC.
- 4.接触电阻:≤0.02Ω.
- 5.绝缘电阻:≥100MΩ

序号	品名	材质
①	0.5 Pitch C型单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型单槽立式BTB母座端子	铜合金/表面点镀金