







RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

High photosynthesis (H)	合高	The female seat neight 母座半高 (H1)	The male seat neight 座半高 (H2)	Insertion height (H3)
3.00		2.20	0.80	1.60
3.50		2.20	1.30	1.60
4.00		3.00	1.00	1.90
4.50		3.50	1.00	1.90
5.00		4.00	1.00	1.90
5.50		4.50	1.00	1.90
6.00		4.00	2.00	1.90
6.50		4.50	2.00	1.90
7.00		3.00	4.00	1.90
7.50		3.50	4.00	1.90
8.00		4.00	4.00	1.90
8.50		4.50	4.00	1.90

序号	品名	材质
①	0.5 Pitch 双槽立式 BTB公座胶芯	PA10T UL94 V-0 颜色: 黑色
②	0.5 Pitch 双槽立式 BTB公座端子	铜合金 / 表面点镀金
③	0.5 Pitch 双槽立式 BTB公座吸盖	LCP UL94 V-0 颜色: 黑色

MEASURE POINT:		联晟欣连接器（深圳）有限公司					
QUADRANT POINT	(QP)	Lianshengxin Connector (Shenzhen) Co., Ltd					
TANGENCY POINT	(TP)						
INTERSECTION POINT	(IP)						
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:	
X.	±0.25	CHECKED		DATE		0.5 Pitch双槽立式BTB公(单高1.0)	
X.x	±0.20	APPROVED		DATE			
X.xx	±0.15	PART NO: LCK-BTG0510-XXPSLYR-GO				REV: 04	SCALE: 1:1
ANGULAR	±3°	DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1

RoHS Compliant

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
LCK-BTG0510-8PSLYR-GO	8	1.50	2.50	4.70	3.40	4.00
LCK-BTG0510-10PSLYR-GO	10	2.00	3.00	5.20	3.90	
LCK-BTG0510-12PSLYR-GO	12	2.50	3.50	5.70	4.40	
LCK-BTG0510-14PSLYR-GO	14	3.00	4.00	6.20	4.90	
LCK-BTG0510-16PSLYR-GO	16	3.50	4.50	6.70	5.40	
LCK-BTG0510-18PSLYR-GO	18	4.00	5.00	7.20	5.90	
LCK-BTG0510-20PSLYR-GO	20	4.50	5.50	7.70	6.40	
LCK-BTG0510-22PSLYR-GO	22	5.00	6.00	8.20	6.90	
LCK-BTG0510-24PSLYR-GO	24	5.50	6.50	8.70	7.40	
LCK-BTG0510-26PSLYR-GO	26	6.00	7.00	9.20	7.90	
LCK-BTG0510-28PSLYR-GO	28	6.50	7.50	9.70	8.40	8.00
LCK-BTG0510-30PSLYR-GO	30	7.00	8.00	10.20	8.90	
LCK-BTG0510-32PSLYR-GO	32	7.50	8.50	10.70	9.40	
LCK-BTG0510-34PSLYR-GO	34	8.00	9.00	11.20	9.90	
LCK-BTG0510-36PSLYR-GO	36	8.50	9.50	11.70	10.40	
LCK-BTG0510-38PSLYR-GO	38	9.00	10.00	12.20	10.90	
LCK-BTG0510-40PSLYR-GO	40	9.50	10.50	12.70	11.40	
LCK-BTG0510-44PSLYR-GO	44	10.50	11.50	13.70	12.40	
LCK-BTG0510-50PSLYR-GO	50	12.00	13.00	15.20	13.90	
LCK-BTG0510-60PSLYR-GO	60	14.50	15.50	17.70	16.40	
LCK-BTG0510-70PSLYR-GO	70	17.00	18.00	20.20	18.90	
LCK-BTG0510-80PSLYR-GO	80	19.50	20.50	22.70	21.40	
LCK-BTG0510-100PSLYR-GO	100	24.50	25.50	27.70	26.40	

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)				 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:				TITLE:			
X. ±0.25				DESIGN	Andy	DATE	2014.12.24
X.x ±0.20				CHECKED		DATE	
X.xx ±0.15				APPROVED		DATE	
ANGULAR ±3°				PART NO: LCK-BTG0510-XXPSLYR-GO			
				REV: 04			
				SCALE: 1:1			
				UNIT: mm			
				DRAWING NO: 102022802			
				SIZE: A4			
				SHEET: 1/1			
							