

RoHS Compliant

NOTES:

1.MATERIAL:






- 1.1 HOUSING:LCP 30% G/F UL94V-0
- 1.2 COLOR:BLACK
- 1.3 CONTACT:BRASS T=0.25mm

2.FINISH:



- 2.1 CONTACT:GOLD FLASH PLATING ON CONTACT AREA
- 2.2 100u"MIN.TIN PLATING ON SOLDERTAILS
- 2.3 50u"MIN.NICKEL UNDERPLATING OVER ALL
- 2.4 BOARD LOCK:100u"MIN.TIN PLATING ON SOLDERTAILS
- 2.5 50u"MIN.NICKEL UNDERPLATING OVEER ALL

3.ELECTRICAL:

- 3.1 CURRENT RATING:1.5 AMPERE PER CONTACT
- 3.2 CONTACT RESISTANCE:30 mΩ MAX
- 3.3 INSULATION RESISTANCE:1000 MΩ MIN
- 3.4 DIELECTRIC WITH STANDING VOVTAGE:500 VDC
- 3.5 OPERATING TEMPERATURE: -40°C ~ +85°C



RECOMMEND PCB LAYOUT
PCB TOLERANCE:±0.05



环保要求		产品必须符合ROHS要求						
3	Peg	Brass C2680		Tin/Ni Plated				
2	Terminal	Brass C2680		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT (QP)								
TANGENCY POINT (TP)								
INTERSECTION POINT (IP)								
UNLESS OTHERWISE SPECIFIED,TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X. ±0.25		CHECKED		DATE		SATA 15P 公座90度DIP型带鱼叉		
X.x ±0.20		APPROVED		DATE				
X.xx ±0.15		PART NO: LCK-STA-06M15P-BG0						
ANGULAR ±3°		DRAWING NO: 102022802				REV: 04	SCALE: 1:1	UNIT: mm
		SIZE: A4				SHEET: 1/1		