








RoHS Compliant



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

1.4 PEG: C2680R-H, T=0.50mm

2.FINISH:

2.1 CONTACT: 1u"/3u"/5u"/15u" GOLDPLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG: 100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL

环境要求		产品必须符合ROHS要求						
3	Peg	Brass C2680R-H		Tin/Ni Plated				
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X. ±0.25		CHECKED		DATE		SATA 7+15P 母座 DIP 180°双排叉鱼叉加长型 针长2.70		
X.x ±0.20		APPROVED		DATE				
X.xx ±0.15		PART NO: LCK-STA-019F22P-BG0				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR ±3°		DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	