






RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

序号	品名	材质
①	0.5 Pitch D型 单槽侧插BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.5 Pitch D型 单槽侧插BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
LCK-BTG0533-4PDLYR-GO	2*2	0.50	2.50	2.50	1.70
LCK-BTG0533-6PDLYR-GO	2*3	1.00	3.00	3.00	2.20
LCK-BTG0533-8PDLYR-GO	2*4	1.50	3.50	3.50	2.70
LCK-BTG0533-10PDLYR-GO	2*5	2.00	4.00	4.00	3.20
LCK-BTG0533-12PDLYR-GO	2*6	2.50	4.50	4.50	3.70
LCK-BTG0533-14PDLYR-GO	2*7	3.00	5.00	5.00	4.20
LCK-BTG0533-16PDLYR-GO	2*8	3.50	5.50	5.50	4.70
LCK-BTG0533-18PDLYR-GO	2*9	4.00	6.00	6.00	5.20
LCK-BTG0533-20PDLYR-GO	2*10	4.50	6.50	6.50	5.70
LCK-BTG0533-22PDLYR-GO	2*11	5.00	7.00	7.00	6.20
LCK-BTG0533-24PDLYR-GO	2*12	5.50	7.50	7.50	6.70
LCK-BTG0533-26PDLYR-GO	2*13	6.00	8.00	8.00	7.20
LCK-BTG0533-28PDLYR-GO	2*14	6.50	8.50	8.50	7.70
LCK-BTG0533-30PDLYR-GO	2*15	7.00	9.00	9.00	8.20
LCK-BTG0533-32PDLYR-GO	2*16	7.50	9.50	9.50	8.70
LCK-BTG0533-34PDLYR-GO	2*17	8.00	10.00	10.00	9.20
LCK-BTG0533-36PDLYR-GO	2*18	8.50	10.50	10.50	9.70
LCK-BTG0533-38PDLYR-GO	2*19	9.00	11.00	11.00	10.20
LCK-BTG0533-40PDLYR-GO	2*20	9.50	11.50	11.50	10.70
.....	...	...	...	...	...
LCK-BTG0533-80PDLYR-GO	2*40	19.50	21.50	21.50	20.70

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	(QP) (TP) (IP)	联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24
X. ±0.25		CHECKED		DATE	
X.x ±0.20		APPROVED		DATE	
X.xx ±0.15		PART NO:	LCK-BTG0533-XXPDLYR-GO	REV:	04
ANGULAR ±3°		DRAWING NO:	102022802	SCALE:	1:1
				UNIT:	mm
				SHEET:	1/1