







RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



序号	品名	材质
①	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色: 黑色
②	0.5 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式BTB母座吸盘	LCP UL94 V-0颜色: 黑色。

High photosynthesis 合高 (H)	The female seat height 母座单高 (H1)	The male seat height 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ± 0.25
X.x ± 0.20
X.xx ± 0.15
ANGULAR $\pm 3^{\circ}$



联晟欣连接器 (深圳) 有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.5Pitch双槽立式BTB母(单高2.2)无柱		
CHECKED		DATE		REV:	04	SCALE:	1:1
APPROVED		DATE		UNIT:	mm		
PART NO: LCK-BTY0522-XXPSLWRGO				SIZE:	A4	SHEET:	1/1
DRAWING NO: 102022802							

RoHS Compliant

PIN NO	PIN	DIM A	DIM B	DIM C	DIM E
LCK-BTY0522-8PSLWRGO	8	1.50	2.55	4.70	4.00
LCK-BTY0522-10PSLWRGO	10	2.00	3.05	5.20	
LCK-BTY0522-12PSLWRGO	12	2.50	3.55	5.70	
LCK-BTY0522-14PSLWRGO	14	3.00	4.05	6.20	
LCK-BTY0522-16PSLWRGO	16	3.50	4.55	6.70	
LCK-BTY0522-18PSLWRGO	18	4.00	5.05	7.20	
LCK-BTY0522-20PSLWRGO	20	4.50	5.55	7.70	
LCK-BTY0522-22PSLWRGO	22	5.00	6.05	8.20	
LCK-BTY0522-24PSLWRGO	24	5.50	6.55	8.70	
LCK-BTY0522-26PSLWRGO	26	6.00	7.05	9.20	
LCK-BTY0522-28PSLWRGO	28	6.50	7.55	9.70	
LCK-BTY0522-30PSLWRGO	30	7.00	8.05	10.20	
LCK-BTY0522-32PSLWRGO	32	7.50	8.55	10.70	8.00
LCK-BTY0522-34PSLWRGO	34	8.00	9.05	11.20	
LCK-BTY0522-36PSLWRGO	36	8.50	9.55	11.70	
LCK-BTY0522-38PSLWRGO	38	9.00	10.05	12.20	
LCK-BTY0522-40PSLWRGO	40	9.50	10.55	12.70	
LCK-BTY0522-44PSLWRGO	44	10.50	11.55	13.70	
LCK-BTY0522-50PSLWRGO	50	12.00	13.05	15.20	
LCK-BTY0522-60PSLWRGO	60	14.50	15.55	17.70	
LCK-BTY0522-70PSLWRGO	70	17.00	18.05	20.20	
LCK-BTY0522-80PSLWRGO	80	19.50	20.55	22.70	
LCK-BTY0522-100PSLWRGO	100	24.50	25.55	27.70	

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)				 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
UNLESS OTHERWISE SPECIFIED, TOLERANCE:				DESIGN	Andy	DATE	2014.12.24	TITLE:		
X. ±0.25				CHECKED		DATE		0.5Pitch及槽立式BTB等(单高2.2)无柱		
X.x ±0.20				APPROVED		DATE				
X.xx ±0.15				PART NO: LCK-BTY0522-XXPSLWRGO				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR ±3°				DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	