

RoHS Compliant

SPECIFICATION:









1.MATERIAL:

- 1.1 HOUSING:LCP UL 94V-0
- 1.2 COLOR:BLACK
- 1.3 CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm
- 1.4 PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:

- 2.1 CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA
- 2.2 100u" TIN PLATING ON SOLDER TAILS
- 2.3 30u" NICKEL UNDERPLATING OVER ALL
- 2.4 PEG:100u" TIN PLATING ON SOLDER TAILS
- 2.5 30u" NICKEL UNDERPLATING OVER ALL

ITEM	DIM A	形状	DIM B
SATA-09M-22BWB-C21	2.10		2.08
SATA-09M-22BWB-C23	2.30		



环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680R—H		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R—H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V—0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MEASURE POINT: QUADRANT POINT (QP) TANGERCY POINT (TP) INTERSECTION POINT (IP)		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd		
UNLESS OTHERWISE SPECIFIED,TOLERANCE:		DESIGN	Andy	DATE
X.	±0.25	CHECKED		DATE
X.x	±0.20	APPROVED		DATE
X.xx	±0.15	PART NO: LCK—STA—015F22P—BG0		REV: 04
ANGULAR	±3°	DRAWING NO: 102022802		SCALE: 1:1
		SIZE: A4		SHEET: 1/1
		TITLE: SATA 7+15P 母座板上5.0SMT		
		UNIT: mm		
				