






RoHS Compliant




High photosynthesis 合金(H)	The female seat neight 插座高度(H1)	The male seat neight 公座高度(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



适用线路板

Part No	CKT	A	B	C	D	E
LCK-BTG0810-8PSLYR-GO	8	2.40	3.45	5.10	4.20	4.00
LCK-BTG0810-10PSLYR-GO	10	3.20	4.25	5.90	5.00	
LCK-BTG0810-12PSLYR-GO	12	4.00	5.05	6.70	5.80	
LCK-BTG0810-14PSLYR-GO	14	4.80	5.85	7.50	6.60	
LCK-BTG0810-16PSLYR-GO	16	5.60	6.65	8.30	7.40	
LCK-BTG0810-18PSLYR-GO	18	6.40	7.45	9.10	8.20	
LCK-BTG0810-20PSLYR-GO	20	7.20	8.25	9.90	9.00	
LCK-BTG0810-22PSLYR-GO	22	8.00	9.05	10.70	9.80	
LCK-BTG0810-24PSLYR-GO	24	8.80	9.85	11.50	10.60	8.00
LCK-BTG0810-26PSLYR-GO	26	9.60	10.65	12.30	11.40	
LCK-BTG0810-28PSLYR-GO	28	10.40	11.45	13.10	12.20	
LCK-BTG0810-30PSLYR-GO	30	11.20	12.25	13.90	13.00	
LCK-BTG0810-32PSLYR-GO	32	12.00	13.05	14.70	13.80	
LCK-BTG0810-34PSLYR-GO	34	12.80	13.85	15.50	14.60	
LCK-BTG0810-36PSLYR-GO	36	13.6	14.65	16.30	15.40	
LCK-BTG0810-38PSLYR-GO	38	14.40	15.45	17.10	16.20	
LCK-BTG0810-40PSLYR-GO	40	15.20	16.25	17.90	17.00	
LCK-BTG0810-44PSLYR-GO	44	16.80	17.85	19.50	18.60	
LCK-BTG0810-50PSLYR-GO	50	19.20	20.25	21.90	21.00	
LCK-BTG0810-60PSLYR-GO	60	23.20	24.25	25.90	25.00	
LCK-BTG0810-70PSLYR-GO	70	27.20	28.25	29.90	29.00	
LCK-BTG0810-80PSLYR-GO	80	31.20	32.25	33.90	33.00	
LCK-BTG0810-100PSLYR-GO	100	39.20	40.25	41.90	41.00	

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.8 Pitch 双槽立式 BTB 公座业务图(单高1.0)
CHECKED		DATE			
APPROVED		DATE			
PART NO: LCK-BTG0810-XXPSLYR-GO				REV: 04	SCALE: 1:1
DRAWING NO: 102022802				UNIT: mm	
				SIZE: A4	SHEET: 1/1