



RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100\text{M}\Omega$

合高(H)	公座单高	母座单高
1.5	1.3	1.4
2.0	1.3	1.9
2.5	1.3	2.4

序号	品名	材质
①	0.5 Pitch C型 单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型 单槽立式BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C
LCK-BTG0513-10PDLWR-GO	2X5	2.00	3.40	5.50
LCK-BTG0513-12PDLWR-GO	2X6	2.50	3.90	6.00
LCK-BTG0513-14PDLWR-GO	2X7	3.00	4.40	6.50
LCK-BTG0513-16PDLWR-GO	2X8	3.50	4.90	7.00
LCK-BTG0513-18PDLWR-GO	2X9	4.00	5.40	7.50
LCK-BTG0513-20PDLWR-GO	2X10	4.50	5.90	8.00
LCK-BTG0513-22PDLWR-GO	2X11	5.00	6.40	8.50
LCK-BTG0513-24PDLWR-GO	2X12	5.50	6.90	9.00
LCK-BTG0513-26PDLWR-GO	2X13	6.00	7.40	9.50
LCK-BTG0513-28PDLWR-GO	2X14	6.50	7.90	10.00
LCK-BTG0513-30PDLWR-GO	2X15	7.00	8.40	10.50
LCK-BTG0513-32PDLWR-GO	2X16	7.50	8.90	11.00
LCK-BTG0513-34PDLWR-GO	2X17	8.00	9.40	11.50
LCK-BTG0513-36PDLWR-GO	2X18	8.50	9.90	12.00
LCK-BTG0513-38PDLWR-GO	2X19	9.00	10.40	12.50
LCK-BTG0513-40PDLWR-GO	2X20	9.50	10.90	13.00
.....	...	...	...	...
LCK-BTG0513-100PDLWR-GO	2X50	24.50	25.90	28.00

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT



UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ± 0.25
X.x ± 0.20
X.xx ± 0.15
ANGULAR $\pm 3^{\circ}$

 联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd				
DESIGN	Andy	DATE	2014.12.24	TITLE:
CHECKED		DATE		0.5 Pitch C型单槽立式BTB公座业务图(单高1.3)
APPROVED		DATE		
PART NO:	LCK-BTG0513-XXPDLWR-GO	REV:	04	SCALE: 1:1
DRAWING NO:	102022802	SIZE:	A4	UNIT: mm
		SHEET:	1/1	