






RoHS Compliant

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

序号	品名	材质
①	0.5 Pitch B型单排 立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型单排 立式BTB公座端子	铜合金/表面镀锡/表面点镀金
③	0.5 Pitch B型单排 立式BTB公座弹片	铜合金/表面镀锡

Part No	CKT	A	B	C	D	E
LCK-BTG0522-10PDLYC-GO	2X5	2.00	3.10	4.60	5.52	4.10
LCK-BTG0522-12PDLYC-GO	2X6	2.50	3.60	5.10	6.02	4.60
LCK-BTG0522-14PDLYC-GO	2X7	3.00	4.10	5.60	6.52	5.10
LCK-BTG0522-16PDLYC-GO	2X8	3.50	4.60	6.10	7.02	5.60
LCK-BTG0522-18PDLYC-GO	2X9	4.00	5.10	6.60	7.52	6.10
LCK-BTG0522-20PDLYC-GO	2X10	4.50	5.60	7.10	8.02	6.60
LCK-BTG0522-22PDLYC-GO	2X11	5.00	6.10	7.60	8.52	7.10
LCK-BTG0522-24PDLYC-GO	2X12	5.50	6.60	8.10	9.02	7.60
LCK-BTG0522-26PDLYC-GO	2X13	6.00	7.10	8.60	9.52	8.10
LCK-BTG0522-28PDLYC-GO	2X14	6.50	7.60	9.10	10.02	8.60
LCK-BTG0522-30PDLYC-GO	2X15	7.00	8.10	9.60	10.52	9.10
LCK-BTG0522-32PDLYC-GO	2X16	7.50	8.60	10.10	11.02	9.60
LCK-BTG0522-34PDLYC-GO	2X17	8.00	9.10	10.60	11.52	10.10
LCK-BTG0522-36PDLYC-GO	2X18	8.50	9.60	11.10	12.02	10.60
LCK-BTG0522-38PDLYC-GO	2X19	9.00	10.10	11.60	12.52	11.10
LCK-BTG0522-40PDLYC-GO	2X20	9.50	10.60	12.10	13.02	11.60
LCK-BTG0522-44PDLYC-GO	2X22	10.50	11.6	13.1	14.02	12.60
LCK-BTG0522-50PDLYC-GO	2X25	12.00	13.1	14.6	15.52	14.10
LCK-BTG0522-60PDLYC-GO	2X30	14.50	15.6	17.1	18.02	16.60
LCK-BTG0522-70PDLYC-GO	2X35	17.00	18.1	19.6	20.52	19.10
LCK-BTG0522-80PDLYC-GO	2X40	19.50	20.6	22.1	23.02	21.60

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)
UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°

联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd					
DESIGN	Andy	DATE	2014.12.24	TITLE: 0.5 Pitch B型单排立式BTB公座业务图(单高2.2)	
CHECKED		DATE			
APPROVED		DATE			
PART NO:	LCK-BTG0522-XXPDLYC-GO	REV:	04	SCALE:	1:1
DRAWING NO:	102022802	SIZE:	A4	SHEET:	1/1