







RoHS Compliant



ITEM	DIM A	形状	DIM B
SATA-08M-22BWB-C21	2.10		2.08
SATA-08M-22BWB-C23	2.30		



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:


2.1 CONTACT:1u"3u"5u"15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



RECOMMEND PCB LAYOUT (T=1.2)
PCB TOLERANCE: ±0.05

环境要求		产品必须符合ROHS要求						
3	Peg	Brass C2680R-H		Tin/Ni Plated				
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT								
TANGENCY POINT								
INTERSECTION POINT								
UNLESS OTHERWISE SPECIFIED,TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X. ±0.25		CHECKED		DATE		SATA 7+15P 母座SMT H3.50 板上侧插		
X.x ±0.10		APPROVED		DATE				
X.xx ±0.15		PART NO: LCK-STA-014F22P-BG0				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR ±3°		DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	