


RoHS Compliant



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING:LCP UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT:PHOSPHOR BRONZE C5191R-H,T=0.25mm

1.4 PEG:BRASS C2680R-H,T=0.30mm

2.FINISH:


2.1 CONTACT:1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



环境要求		产品必须符合ROHS要求						
3	Peg	Brass C2680R-H		Tin/Ni Plated				
2	Terminal	Pho.Bronze C5191R		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT	QP							
TANGENCY POINT	TP							
INTERSECTION POINT	IP							
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X.	±0.25	CHECKED		DATE		SATA 7+15P 母座板上6.74 SMT侧插式		
X.x	±0.20	APPROVED		DATE				
X.xx	±0.15	PART NO: LCK-STA-020F22P-BG0				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR	±3°	DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	