

RoHS Compliant









SPECIFICATION:

1.MATERIAL:

- 1.1 HOUSING: LCP E130i 30% G/F UL 94V-0
1.2 COLOR: BLACK
1.3 CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm
1.4 PEG: BRASS C2680R-H, T=0.20mm

2.FINISH:

- 2.1 CONTACT: 1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA
2.2 100u" TIN PLATING ON SOLDER TAILS
2.3 30u" NICKEL UNDERPLATING OVER ALL
2.4 PEG: 100u" TIN PLATING ON SOLDER TAILS
2.5 30u" NICKEL UNDERPLATING OVER ALL



RECOMMENDED PCB LAYOUT
UNLESS
TOLERANCE: +/ - 0.05

环保要求		产品必须符合ROHS要求		
3	Peg	Brass C2680		Tin/Ni Plated
2	Terminal	Pho.Bronze C5191R-H		Gold/Tin Plated
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT



UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器 (深圳) 有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	SATA 7+15P 直立式SMT 带接地片 加盖子		
CHECKED		DATE		REV:	04	SCALE:	1:1
APPROVED		DATE		UNIT:	mm		
PART NO:	LCK-STA-022F22P-LG0			SIZE:	A4	SHEET:	1/1
DRAWING NO:	102022802						