

RoHS Compliant

SPECIFICATION:

1.MATERIAL:






- 1.1 HOUSING:LCP 30% G/F UL 94V-0
1.2 COLOR: BLACK
1.3 CONTACT:BRASS C2680R-H,T=0.25mm
1.4 PEG: BRASS C2680R-H,T=0.30mm

2.FINISH:


- 2.1 CONTACT:1u",3u",5u",15u"GOLD PLATING ON CONTACT AREA
2.2 100u" MIN.TIN PLATING ON SOLDER TAILS
2.3 40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:


- 3.1 CURRENT RATING:1.5 AMPERE PER CONTACT
3.2 CONTACT RESISTANCE:30 MILLIOHMS MAX
3.3 INSULATION RESISTANCE:1000 MEGOHMS MIN
3.4 DIELECTRIC WITH STANDING VOLTAGE:500 VDC
3.5 OPERATING TEMPERATURE: -40°C ~ +85°C
4.THE MARK (XX) DIMENSIONS MUST BE MEASURED BY FAI.



SECTION: X-X



PCB LAYOUT
TOLERANCES: ±0.05MM



SECTION: Y-Y

环保要求		产品必须符合ROHS要求						
3	Peg	Brass C2680		Tin/Ni Plated				
2	Terminal	Brass C2680		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°		DESIGN	Andy	DATE	2014.12.24	TITLE:		
		CHECKED		DATE		SATA7+15P 公座混插式SMT H0.9 (半包式) 接口连接器片		
		APPROVED		DATE				
		PART NO: LCK-STA-021M22P-LG0				REV: 04	SCALE: 1:1	UNIT: mm
		DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	