






RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.03\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

序号	品名	材质
①	0.5 Pitch D型单槽侧插BTB母座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.5 Pitch D型单槽侧插BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
LCK-BTY0553-4PDLYR-GO	2*2	0.50	2.54	3.50	2.20
LCK-BTY0553-6PDLYR-GO	2*3	1.00	3.04	4.00	2.70
LCK-BTY0553-8PDLYR-GO	2*4	1.50	3.54	4.50	3.20
LCK-BTY0553-10PDLYR-GO	2*5	2.00	4.04	5.00	3.70
LCK-BTY0553-12PDLYR-GO	2*6	2.50	4.54	5.50	4.20
LCK-BTY0553-14PDLYR-GO	2*7	3.00	5.04	6.00	4.70
LCK-BTY0553-16PDLYR-GO	2*8	3.50	5.54	6.50	5.20
LCK-BTY0553-18PDLYR-GO	2*9	4.00	6.04	7.00	5.70
LCK-BTY0553-20PDLYR-GO	2*10	4.50	6.54	7.50	6.20
LCK-BTY0553-22PDLYR-GO	2*11	5.00	7.04	8.00	6.70
LCK-BTY0553-24PDLYR-GO	2*12	5.50	7.54	8.50	7.20
LCK-BTY0553-26PDLYR-GO	2*13	6.00	8.04	9.00	7.70
LCK-BTY0553-28PDLYR-GO	2*14	6.50	8.54	9.50	8.20
LCK-BTY0553-30PDLYR-GO	2*15	7.00	9.04	10.00	8.70
LCK-BTY0553-32PDLYR-GO	2*16	7.50	9.54	10.50	9.20
LCK-BTY0553-34PDLYR-GO	2*17	8.00	10.04	11.00	9.70
LCK-BTY0553-36PDLYR-GO	2*18	8.50	10.54	11.50	10.20
LCK-BTY0553-38PDLYR-GO	2*19	9.00	11.04	12.00	10.70
LCK-BTY0553-40PDLYR-GO	2*20	9.50	11.54	12.50	11.20
.....	...	...	...	...	...
LCK-BTY0553-80PDLYR-GO	2*40	19.50	21.54	22.50	21.20

MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd					
QUADRANT POINT	(QP)						
TANGENCY POINT	(TP)						
INTERSECTION POINT	(IP)						
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:	
X.	±0.25	CHECKED		DATE		0.5 Pitch D型单槽侧插BTB母座业务图(单高5.3)	
X.x	±0.20	APPROVED		DATE			
X.xx	±0.15	PART NO: LCK-BTY0553-XXPDLYR-GO				REV: 04	SCALE: 1:1
ANGULAR	±3°	DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1
							