



- NOTE:
- 1.Rating: 24V 25mA DC
 - 2.Contact Resistance: 50mΩ max
 - 3.Dielectric Strength:500V AC/1Minute
 - 4.Operating Force: 1000gf Max
 - 5.Operating Life:2,000 Cycles



PCB Layout(Pattern Side)



Circuit Diagram

④	Terminal		Phosphor bronze	Au Plating
③	Base	1	PBT	Black
②	Cover	1	PBT	Black
①	Keystoke	1	PBT	White

ITEM	PART NAME	QTY.	MATERIAL	FINISHING
------	-----------	------	----------	-----------

APPROVALS		DATE	ECON 德之隆® ELECTRONICS CO.,LTD	
DRAWN	G.M.Chen	2015/6/26		
CHECKED			TITLE: DIP SWITCHES	
APPROVALS			PART NO. EM-01KP	

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.	TOLERANCES ARE	30°±0.1° 10°±0.20° 9°±0°	±0.30 ±0.20 ±0.13	ANGLE	UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
	A		NEW					±2°	±0.10		DRAWING NO.		PROJ. ①