

RoHS Compliant

SPECIFICATION:

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

1.4 PEG: BRASS C2680R-H, T=0.30mm

2.FINISH:







2.1 CONTACT: 1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDER TAILS



2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG: 100u" TIN PLATING ON SOLDER TAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



SEC A
SCALE 3:1



ITEM	DIM A
SATA-03M-22AWZ-C21	2.10
SATA-03M-22AWZ-C23	2.30
SATA-03M-22AWZ-C245	2.45
SATA-03M-22AWZ-C259	2.59

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	GP TP IP	 联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN: Andy CHECKED: APPROVED: PART NO: LCK-STA-09F22P-BG0 DRAWING NO: 102022802
X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	DATE: 2014.12.24 DATE: DATE: REV: 04 SCALE: 1:1 UNIT: mm	TITLE: SATA 7+15P 母座板下6.74DIP SHEET: 1/1