



RoHS Compliant



Part No	CKT	A	B	C
LCK-BTG0867-20PDLYR-GO	2*10	7.20	13.80	12.20
LCK-BTG0867-22PDLYR-GO	2*11	8.00	14.60	13.00
LCK-BTG0867-24PDLYR-GO	2*12	8.80	15.40	13.80
LCK-BTG0867-26PDLYR-GO	2*13	9.60	16.20	14.60
LCK-BTG0867-28PDLYR-GO	2*14	10.40	17.00	15.40
LCK-BTG0867-30PDLYR-GO	2*15	11.20	17.80	16.20
LCK-BTG0867-32PDLYR-GO	2*16	12.00	18.60	17.00
LCK-BTG0867-34PDLYR-GO	2*17	12.80	19.40	17.80
LCK-BTG0867-36PDLYR-GO	2*18	13.60	20.20	18.60
LCK-BTG0867-38PDLYR-GO	2*19	14.40	21.00	19.40
LCK-BTG0867-40PDLYR-GO	2*20	15.20	21.80	20.20
LCK-BTG0867-42PDLYR-GO	2*21	16.00	22.60	21.00
LCK-BTG0867-44PDLYR-GO	2*22	16.80	23.40	21.80
LCK-BTG0867-46PDLYR-GO	2*23	17.60	24.20	22.60
LCK-BTG0867-48PDLYR-GO	2*24	18.40	25.00	23.40
LCK-BTG0867-50PDLYR-GO	2*25	19.20	25.80	24.20
.....	...	...	...	...
LCK-BTG0867-200PDLYR-GO	2*100	79.20	85.80	84.20

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: -40°C~85°C.
3. 额定电压: 100V, AC.
4. 接触电阻: ≤0.05Ω.
5. 绝缘电阻: ≥500MΩ

序号	品名	材质
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金
③	0.8 Pitch B型立式 BTB公座吸盘	不锈钢

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT




UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.8 Pitch B型立式BTB公座端子图(单端6.7)		
CHECKED		DATE		REV:	04	SCALE:	1:1
APPROVED		DATE		UNIT:	mm		
PART NO: LCK-BTG0867-XXPDLYR-GO				SIZE:	A4	SHEET:	1/1
DRAWING NO: 102022802							

RoHS Compliant



MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN Andy DATE 2014.12.24
CHECKED DATE
APPROVED DATE

PART NO: LCK-BTG0867-XXPDLYR-GO
DRAWING NO:

TITLE:
0.8 Pitch B型立式BTB公座兼母座(单高6.7)

REV: 04 SCALE: 1:1 UNIT: mm
SIZE: A4 SHEET: 1/1