





RoHS Compliant



技术指标:


1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4



适用线路板

序号	品名	材质
①	0.5 Pitch B型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型 单槽立式BTB母座端子	铜合金/表面镀锡/表面点镀金



Part No	CKT	A	B	C	D
LCK-BTY0522-10PDLYRGO	2X5	2.00	3.20	4.70	4.10
LCK-BTY0522-12PDLYRGO	2X6	2.50	3.70	5.20	4.60
LCK-BTY0522-14PDLYRGO	2X7	3.00	4.20	5.70	5.10
LCK-BTY0522-16PDLYRGO	2X8	3.50	4.70	6.20	5.60
LCK-BTY0522-18PDLYRGO	2X9	4.00	5.20	6.70	6.10
LCK-BTY0522-20PDLYRGO	2X10	4.50	5.70	7.20	6.60
LCK-BTY0522-22PDLYRGO	2X11	5.00	6.20	7.70	7.10
LCK-BTY0522-24PDLYRGO	2X12	5.50	6.70	8.20	7.60
LCK-BTY0522-26PDLYRGO	2X13	6.00	7.20	8.70	8.10
LCK-BTY0522-28PDLYRGO	2X14	6.50	7.70	9.20	8.60
LCK-BTY0522-30PDLYRGO	2X15	7.00	8.20	9.70	9.10
LCK-BTY0522-32PDLYRGO	2X16	7.50	8.70	10.20	9.60
LCK-BTY0522-34PDLYRGO	2X17	8.00	9.20	10.70	10.10
LCK-BTY0522-36PDLYRGO	2X18	8.50	9.70	11.20	10.60
LCK-BTY0522-38PDLYRGO	2X19	9.00	10.20	11.70	11.10
LCK-BTY0522-40PDLYRGO	2X20	9.50	10.70	12.20	11.60
LCK-BTY0522-44PDLYRGO	2X22	10.50	11.70	13.20	12.60
LCK-BTY0522-50PDLYRGO	2X25	12.00	13.20	14.70	14.10
LCK-BTY0522-60PDLYRGO	2X30	14.50	15.70	17.20	16.60
LCK-BTY0522-70PDLYRGO	2X35	17.00	18.20	19.70	19.10
LCK-BTY0522-80PDLYRGO	2X40	19.50	20.70	22.20	21.60

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	GP TP IP	联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	DESIGN CHECKED APPROVED	Andy DATE DATE	DATE DATE	TITLE: 0.5 Pitch B型单槽立式BTB母座业务图 (单槽2.2)无牌片点镀金	
X. X.x X.xx ANGULAR	±0.25 ±0.20 ±0.15 ±3°	PART NO: LCK-BTY0522-XXPDLYR-GO DRAWING NO: 102022802		REV: 04 SIZE: A4	SCALE: 1:1 SHEET: 1/1