






RoHS Compliant

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

序号	品名	材质
①	0.5 Pitch B型 单槽立式BTB公座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型 单槽立式BTB公座端子	铜合金/表面点镀金

Part No	CKT	A	B	C	D
LCK-BTG0526-8PDLYR-GO	2X4	1.50	2.60	4.10	3.60
LCK-BTG0526-10PDLYR-GO	2X5	2.00	3.10	4.60	4.10
LCK-BTG0526-12PDLYR-GO	2X6	2.50	3.60	5.10	4.60
LCK-BTG0526-14PDLYR-GO	2X7	3.00	4.10	5.60	5.10
LCK-BTG0526-16PDLYR-GO	2X8	3.50	4.60	6.10	5.60
LCK-BTG0526-18PDLYR-GO	2X9	4.00	5.10	6.60	6.10
LCK-BTG0526-20PDLYR-GO	2X10	4.50	5.60	7.10	6.60
LCK-BTG0526-22PDLYR-GO	2X11	5.00	6.10	7.60	7.10
LCK-BTG0526-24PDLYR-GO	2X12	5.50	6.60	8.10	7.60
LCK-BTG0526-26PDLYR-GO	2X13	6.00	7.10	8.60	8.10
LCK-BTG0526-28PDLYR-GO	2X14	6.50	7.60	9.10	8.60
LCK-BTG0526-30PDLYR-GO	2X15	7.00	8.10	9.60	9.10
LCK-BTG0526-32PDLYR-GO	2X16	7.50	8.60	10.10	9.60
LCK-BTG0526-34PDLYR-GO	2X17	8.00	9.10	10.60	10.10
LCK-BTG0526-36PDLYR-GO	2X18	8.50	9.60	11.10	10.60
LCK-BTG0526-38PDLYR-GO	2X19	9.00	10.10	11.60	11.10
LCK-BTG0526-40PDLYR-GO	2X20	9.50	10.60	12.10	11.60
LCK-BTG0526-44PDLYR-GO	2X22	10.50	11.60	13.10	12.60
LCK-BTG0526-50PDLYR-GO	2X25	12.00	13.10	14.60	14.10
LCK-BTG0526-60PDLYR-GO	2X30	14.50	15.60	17.10	16.60
LCK-BTG0526-70PDLYR-GO	2X35	17.00	18.10	19.60	19.10
LCK-BTG0526-80PDLYR-GO	2X40	19.50	20.60	22.10	21.60

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	GP TP IP	 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd							
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:			
X. ±0.25		CHECKED		DATE		0.5 Pitch B型单槽立式BTB公座业务图(单高2.6)无牌片镀金			
X.x ±0.20		APPROVED		DATE					
X.xx ±0.15		PART NO: LCK-BTG0526-XXPDLYR-GO				REV: 04	SCALE: 1:1	UNIT: mm	
ANGULAR ±3°		DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1		