







RoHS Compliant



- 技术指标:
1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
 2. 温度范围: -40°C~85°C.
 3. 额定电压: 50V, AC.
 4. 接触电阻: $\leq 0.02\Omega$.
 5. 绝缘电阻: $\geq 100M\Omega$



序号	品名	材质
①	0.5 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0 颜色: 黑色
②	0.5 Pitch双槽立式BTB母座端子	铜合金 / 表面点镀金
③	0.5 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0颜色: 黑色.

High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT

GP
TP
IP

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:

X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°

DESIGN: Andy
CHECKED:
APPROVED:
DATE: 2014.12.24
DATE:
DATE:
TITLE: 0.5Pitch双槽立式BTB母(单高3.0)无桩

PART NO: LCK-BTY0530-XXPSLWR-GO
DRAWING NO: 102022802

REV: 04
SCALE: 1:1
UNIT: mm

SIZE: A4
SHEET: 1/1



RoHS Compliant

PIN NO	PIN	DIM A	DIM B	DIM C	DIM E
LCK-BTY0530-8PSLWR-GO	8	1.50	2.55	4.70	4.00
LCK-BTY0530-10PSLWR-GO	10	2.00	3.05	5.20	
LCK-BTY0530-12PSLWR-GO	12	2.50	3.55	5.70	
LCK-BTY0530-14PSLWR-GO	14	3.00	4.05	6.20	
LCK-BTY0530-16PSLWR-GO	16	3.50	4.55	6.70	
LCK-BTY0530-18PSLWR-GO	18	4.00	5.05	7.20	
LCK-BTY0530-20PSLWR-GO	20	4.50	5.55	7.70	
LCK-BTY0530-22PSLWR-GO	22	5.00	6.05	8.20	
LCK-BTY0530-24PSLWR-GO	24	5.50	6.55	8.70	
LCK-BTY0530-26PSLWR-GO	26	6.00	7.05	9.20	
LCK-BTY0530-28PSLWR-GO	28	6.50	7.55	9.70	8.00
LCK-BTY0530-30PSLWR-GO	30	7.00	8.05	10.20	
LCK-BTY0530-32PSLWR-GO	32	7.50	8.55	10.70	
LCK-BTY0530-34PSLWR-GO	34	8.00	9.05	11.20	
LCK-BTY0530-36PSLWR-GO	36	8.50	9.55	11.70	
LCK-BTY0530-38PSLWR-GO	38	9.00	10.05	12.20	
LCK-BTY0530-40PSLWR-GO	40	9.50	10.55	12.70	
LCK-BTY0530-44PSLWR-GO	44	10.50	11.55	13.70	
LCK-BTY0530-50PSLWR-GO	50	12.00	13.05	15.20	
LCK-BTY0530-60PSLWR-GO	60	14.50	15.55	17.70	
LCK-BTY0530-70PSLWR-GO	70	17.00	18.05	20.20	
LCK-BTY0530-80PSLWR-GO	80	19.50	20.55	22.70	
LCK-BTY0530-100PSLWR-GO	100	24.50	25.55	27.70	

MEASURE POINT: 				 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT 										
TANGENCY POINT 										
INTERSECTION POINT 										
UNLESS OTHERWISE SPECIFIED, TOLERANCE:				DESIGN	Andy	DATE	2014.12.24	TITLE:		
X. ±0.25				CHECKED		DATE		0.5Pitch双槽立式BTB母(单高3.0)无柱		
X.x ±0.20				APPROVED		DATE				
X.xx ±0.15				PART NO: LCK-BTY0530-XXPSLWR-GO				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR ±3°				DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	