







RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: $\leq 0.02\Omega$.
5. 绝缘电阻: $\geq 100M\Omega$

序号	品名	材质
①	0.5 Pitch双槽立式 BTB母座胶芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式 BTB母座吸盖	LCP UL94 V-0颜色:黑色.



High photosynthesis 合高 (H)	The female seat neight 母座单高 (H1)	The male seat neight 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	QP TP IP	 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd																													
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	<table><tr><td>DESIGN</td><td>Andy</td><td>DATE</td><td>2014.12.24</td></tr><tr><td>CHECKED</td><td></td><td>DATE</td><td></td></tr><tr><td>APPROVED</td><td></td><td>DATE</td><td></td></tr><tr><td colspan="4">PART NO: LCK-BTY0530-XXPSLYR-GO</td></tr><tr><td colspan="4">DRAWING NO: 102022802</td></tr></table>	DESIGN	Andy	DATE	2014.12.24	CHECKED		DATE		APPROVED		DATE		PART NO: LCK-BTY0530-XXPSLYR-GO				DRAWING NO: 102022802				<table><tr><td colspan="3">TITLE: 0.5 Pitch双槽立式BTB母(单高3.0)</td></tr><tr><td>REV: 04</td><td>SCALE: 1:1</td><td>UNIT: mm</td></tr><tr><td>SIZE: A4</td><td>SHEET: 1/1</td><td></td></tr></table>	TITLE: 0.5 Pitch双槽立式BTB母(单高3.0)			REV: 04	SCALE: 1:1	UNIT: mm	SIZE: A4	SHEET: 1/1	
DESIGN	Andy	DATE	2014.12.24																												
CHECKED		DATE																													
APPROVED		DATE																													
PART NO: LCK-BTY0530-XXPSLYR-GO																															
DRAWING NO: 102022802																															
TITLE: 0.5 Pitch双槽立式BTB母(单高3.0)																															
REV: 04	SCALE: 1:1	UNIT: mm																													
SIZE: A4	SHEET: 1/1																														

RoHS Compliant

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
LCK-BTY0530-8PSLYR-GO	8	1.50	2.55	4.70	3.40	4.00
LCK-BTY0530-10PSLYR-GO	10	2.00	3.05	5.20	3.90	
LCK-BTY0530-12PSLYR-GO	12	2.50	3.55	5.70	4.40	
LCK-BTY0530-14PSLYR-GO	14	3.00	4.05	6.20	4.90	
LCK-BTY0530-16PSLYR-GO	16	3.50	4.55	6.70	5.40	
LCK-BTY0530-18PSLYR-GO	18	4.00	5.05	7.20	5.90	
LCK-BTY0530-20PSLYR-GO	20	4.50	5.55	7.70	6.40	
LCK-BTY0530-22PSLYR-GO	22	5.00	6.05	8.20	6.90	
LCK-BTY0530-24PSLYR-GO	24	5.50	6.55	8.70	7.40	
LCK-BTY0530-26PSLYR-GO	26	6.00	7.05	9.20	7.90	
LCK-BTY0530-28PSLYR-GO	28	6.50	7.55	9.70	8.40	
LCK-BTY0530-30PSLYR-GO	30	7.00	8.05	10.20	8.90	
LCK-BTY0530-32PSLYR-GO	32	7.50	8.55	10.70	9.40	8.00
LCK-BTY0530-34PSLYR-GO	34	8.00	9.05	11.20	9.90	
LCK-BTY0530-36PSLYR-GO	36	8.50	9.55	11.70	10.40	
LCK-BTY0530-38PSLYR-GO	38	9.00	10.05	12.20	10.90	
LCK-BTY0530-40PSLYR-GO	40	9.50	10.55	12.70	11.40	
LCK-BTY0530-44PSLYR-GO	44	10.50	11.05	13.70	12.40	
LCK-BTY0530-50PSLYR-GO	50	12.00	13.05	15.20	13.90	
LCK-BTY0530-60PSLYR-GO	60	14.50	15.55	17.70	16.40	
LCK-BTY0530-70PSLYR-GO	70	17.00	18.05	20.20	18.90	
LCK-BTY0530-80PSLYR-GO	80	19.50	20.55	22.70	21.40	
LCK-BTY0530-100PSLYR-GO	100	24.50	25.55	27.70	26.40	

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)				 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:				TITLE:			
X. ±0.25				DESIGN	Andy	DATE	2014.12.24
X.x ±0.20				CHECKED		DATE	
X.xx ±0.15				APPROVED		DATE	
ANGULAR ±3°				PART NO: LCK-BTY0530-XXPSLYR-GO			
				REV: 04			
				SCALE: 1:1			
				UNIT: mm			
				DRAWING NO: 102022802			
				SIZE: A4			
				SHEET: 1/1			
							