






RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 50V, AC.
4. 接触电阻: ≤0.02Ω.
5. 绝缘电阻: ≥100MΩ



适用线路板

High photosynthesis 高 (H)	The female seat height (H1)	The male seat height 公座单高 (H2)	Insertion height (H3)
3.00	2.20	0.80	1.60
3.50	2.20	1.30	1.60
4.00	3.00	1.00	1.90
4.50	3.50	1.00	1.90
5.00	4.00	1.00	1.90
5.50	4.50	1.00	1.90
6.00	4.00	2.00	1.90
6.50	4.50	2.00	1.90
7.00	3.00	4.00	1.90
7.50	3.50	4.00	1.90
8.00	4.00	4.00	1.90
8.50	4.50	4.00	1.90

序号	品名	材质
①	0.5 Pitch双槽立式 BTB公座胶芯	PA10T UL94 V-0 颜色:黑色
②	0.5 Pitch双槽立式 BTB公座端子	铜合金/表面点镀金
③	0.5 Pitch双槽立式 BTB公座吸盘	LCP UL94 V-0颜色:黑色.

MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)	联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	DESIGN CHECKED APPROVED	Andy DATE DATE	DATE 2014.12.24	TITLE: 0.5 Pitch双槽立式BTB公(单高2.0)
PART NO: LCK-BTG0520-XXPSLYR-GO DRAWING NO: 102022802	REV: 04 SCALE: 1:1 UNIT: mm	SIZE: A4 SHEET: 1/1		

RoHS Compliant

PIN NO	PIN	DIM A	DIM B	DIM C	DIM D	DIM E
LCK-BTG0520-8PSLYR-GO	8	1.50	2.50	4.70	3.40	4.00
LCK-BTG0520-10PSLYR-GO	10	2.00	3.00	5.20	3.90	
LCK-BTG0520-12PSLYR-GO	12	2.50	3.50	5.70	4.40	
LCK-BTG0520-14PSLYR-GO	14	3.00	4.00	6.20	4.90	
LCK-BTG0520-16PSLYR-GO	16	3.50	4.50	6.70	5.40	
LCK-BTG0520-18PSLYR-GO	18	4.00	5.00	7.20	5.90	
LCK-BTG0520-20PSLYR-GO	20	4.50	5.50	7.70	6.40	
LCK-BTG0520-22PSLYR-GO	22	5.00	6.00	8.20	6.90	
LCK-BTG0520-24PSLYR-GO	24	5.50	6.50	8.70	7.40	
LCK-BTG0520-26PSLYR-GO	26	6.00	7.00	9.20	7.90	
LCK-BTG0520-28PSLYR-GO	28	6.50	7.50	9.70	8.40	
LCK-BTG0520-30PSLYR-GO	30	7.00	8.00	10.20	8.90	
LCK-BTG0520-32PSLYR-GO	32	7.50	8.50	10.70	9.40	8.00
LCK-BTG0520-34PSLYR-GO	34	8.00	9.00	11.20	9.90	
LCK-BTG0520-36PSLYR-GO	36	8.50	9.50	11.70	10.40	
LCK-BTG0520-38PSLYR-GO	38	9.00	10.00	12.20	10.90	
LCK-BTG0520-40PSLYR-GO	40	9.50	10.50	12.70	11.40	
LCK-BTG0520-44PSLYR-GO	44	10.50	11.50	13.70	12.40	
LCK-BTG0520-50PSLYR-GO	50	12.00	13.00	15.20	13.90	
LCK-BTG0520-60PSLYR-GO	60	14.50	15.50	17.70	16.40	
LCK-BTG0520-70PSLYR-GO	70	17.00	18.00	20.20	18.90	
LCK-BTG0520-80PSLYR-GO	80	19.50	20.50	22.70	21.40	
LCK-BTG0520-100PSLYR-GO	100	24.50	25.50	27.70	26.40	

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT

QP

TP

IP

UNLESS OTHERWISE SPECIFIED,TOLERANCE:

X.±0.25

X.x±0.20

X.xx±0.15

ANGULAR±3°

DESIGN

Andy

DATE

2014.12.24

TITLE:

0.5 Pitch双槽立式BTBA(单高2.0)

PART NO: LCK-BTG0520-XXPSLYR-GO

REV: 04

SCALE: 1:1

UNIT: mm

DRAWING NO: 102022802

SIZE: A4

SHEET: 1/1

联晟欣连接器（深圳）有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd