






RoHS Compliant




技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$.
3. 额定电压: 100V, AC.
4. 接触电阻: $\leq 0.05\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$

序号	品名	材质
①	0.8 Pitch B型立式 BTB插座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch B型立式 BTB插座端子	铜合金/表面点镀金
③	0.8 Pitch B型立式 BTB插座吸盘	不锈钢

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT		GP TP IP	 联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd		TITLE: 0.8 Pitch B型立式BTB插座业务图(标准11.7)	
UNLESS OTHERWISE SPECIFIED, TOLERANCE:						
X.	±0.25	DESIGN	Andy	DATE	2014.12.24	REV: 04
X.x	±0.20	CHECKED		DATE		
X.xx	±0.15	APPROVED		DATE		SCALE: 1:1
ANGULAR	±3°	PART NO:	LCK-BTY08117-XXPDLYR-GO		DRAWING NO: 102022802	UNIT: mm
		SIZE: A4	SHEET: 1/1			

RoHS Compliant



MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	GP TP IP	联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	DESIGN	Andy	DATE	2014.12.24	TITLE: 0.8 Pitch B型立式BTB母座 (Pin 11.7)
	CHECKED		DATE		
	APPROVED		DATE		
	PART NO: LCK-BTY08117-XXPDLYR-GO DRAWING NO: 102022802				REV: 04 SCALE: 1:1 UNIT: mm