





RoHS Compliant




High photosynthesis 台高(H)	The female seat neight 母座单高(H1)	The male seat neight 公座单高(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

序号	品名	材质
①	0.8 Pitch双槽立式 BTB母座胶芯	PA10T UL94 V-0, 颜色: 黑色
②	0.8 Pitch双槽立式 BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式 BTB母座吸盖	LCP UL94 V-0, 颜色: 黑色



Part No	CKT	A	B	C	D	E
LCK-BTY0830-8PSLYR-GO	8	2.40	3.50	5.10	4.20	4.00
LCK-BTY0830-10PSLYR-GO	10	3.20	4.30	5.90	5.00	
LCK-BTY0830-12PSLYR-GO	12	4.00	5.10	6.70	5.80	
LCK-BTY0830-14PSLYR-GO	14	4.80	5.90	7.50	6.60	
LCK-BTY0830-16PSLYR-GO	16	5.60	6.70	8.30	7.40	
LCK-BTY0830-18PSLYR-GO	18	6.40	7.50	9.10	8.20	
LCK-BTY0830-20PSLYR-GO	20	7.20	8.30	9.90	9.00	
LCK-BTY0830-22PSLYR-GO	22	8.00	9.10	10.70	9.80	
LCK-BTY0830-24PSLYR-GO	24	8.80	9.90	11.50	10.60	8.00
LCK-BTY0830-26PSLYR-GO	26	9.60	10.70	12.30	11.40	
LCK-BTY0830-27PSLYR-GO	28	10.40	11.50	13.10	12.20	
LCK-BTY0830-30PSLYR-GO	30	11.20	12.30	13.90	13.00	
LCK-BTY0830-32PSLYR-GO	32	12.00	13.10	14.70	13.80	
LCK-BTY0830-34PSLYR-GO	34	12.80	13.90	15.50	14.60	
LCK-BTY0830-36PSLYR-GO	36	13.6	14.70	16.30	15.40	
LCK-BTY0830-38PSLYR-GO	38	14.40	15.50	17.10	16.20	
LCK-BTY0830-40PSLYR-GO	40	15.20	16.30	17.90	17.00	
LCK-BTY0830-44PSLYR-GO	44	16.80	17.90	19.50	18.60	
LCK-BTY0830-50PSLYR-GO	50	19.20	20.30	21.90	21.00	
LCK-BTY0830-60PSLYR-GO	60	23.20	24.30	25.90	25.00	
LCK-BTY0830-70PSLYR-GO	70	27.20	28.30	29.90	29.00	
LCK-BTY0830-80PSLYR-GO	80	31.20	32.30	33.90	33.00	
LCK-BTY0830-100PSLYR-GO	100	39.20	40.30	41.90	41.00	

MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT	①P ②TP ③IP	联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd	
UNLESS OTHERWISE SPECIFIED, TOLERANCE: X. ±0.25 X.x ±0.20 X.xx ±0.15 ANGULAR ±3°	DESIGN CHECKED APPROVED	Andy DATE DATE	2014.12.24 TITLE: 0.8 Pitch双槽立式BTB母座业务图(单高3.0)
PART NO: LCK-BTY0830-XXPSLYR-GO DRAWING NO: 102022802	REV: 04 SCALE: 1:1 SHEET: 1/1	UNIT: mm	