





RoHS Compliant


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$



合高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4

序号	品名	材质
①	0.5 Pitch B型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch B型 单槽立式BTB母座端子	铜合金/表面镀金



Part No	CKT	A	B	C	D
LCK-BTY0544-10PDLYR-GO	2X5	2.00	3.20	4.70	4.10
LCK-BTY0544-12PDLYR-GO	2X6	2.50	3.70	5.20	4.60
LCK-BTY0544-14PDLYR-GO	2X7	3.00	4.20	5.70	5.10
LCK-BTY0544-16PDLYR-GO	2X8	3.50	4.70	6.20	5.60
LCK-BTY0544-18PDLYR-GO	2X9	4.00	5.20	6.70	6.10
LCK-BTY0544-20PDLYR-GO	2X10	4.50	5.70	7.20	6.60
LCK-BTY0544-22PDLYR-GO	2X11	5.00	6.20	7.70	7.10
LCK-BTY0544-24PDLYR-GO	2X12	5.50	6.70	8.20	7.60
LCK-BTY0544-26PDLYR-GO	2X13	6.00	7.20	8.70	8.10
LCK-BTY0544-28PDLYR-GO	2X14	6.50	7.70	9.20	8.60
LCK-BTY0544-30PDLYR-GO	2X15	7.00	8.20	9.70	9.10
LCK-BTY0544-32PDLYR-GO	2X16	7.50	8.70	10.20	9.60
LCK-BTY0544-34PDLYR-GO	2X17	8.00	9.20	10.70	10.10
LCK-BTY0544-36PDLYR-GO	2X18	8.50	9.70	11.20	10.60
LCK-BTY0544-38PDLYR-GO	2X19	9.00	10.20	11.70	11.10
LCK-BTY0544-40PDLYR-GO	2X20	9.50	10.70	12.20	11.60
LCK-BTY0544-44PDLYR-GO	2X22	10.50	11.70	13.20	12.60
LCK-BTY0544-50PDLYR-GO	2X25	12.00	13.20	14.70	14.10
LCK-BTY0544-60PDLYR-GO	2X30	14.50	15.70	17.20	16.60
LCK-BTY0544-70PDLYR-GO	2X35	17.00	18.20	19.70	19.10
LCK-BTY0544-80PDLYR-GO	2X40	19.50	20.70	22.20	21.60

MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT	(QP)							
TANGENCY POINT	(TP)							
INTERSECTION POINT	(IP)							
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X.	±0.25	CHECKED		DATE		0.5 Pitch B型单槽立式BTB母座业务图(单高4.4)无焊片镀点		
X.x	±0.20	APPROVED		DATE				
X.xx	±0.15	PART NO: LCK-BTY0544-XXPDLYR-GO				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR	±3°	DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	