





RoHS Compliant




适用线路板

技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象.
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压: 100V, AC.
4. 接触电阻: $\leq 0.05\Omega$.
5. 绝缘电阻: $\geq 500\text{M}\Omega$

序号	品名	材质
①	0.8 Pitch B型立式 BTB母座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch B型立式 BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch B型立式 BTB母座吸盘	不锈钢



Part No	CKT	A	B	C
LCK-BTY0837-20PDLYR-GO	2*10	7.20	13.80	12.20
LCK-BTY0837-22PDLYR-GO	2*11	8.00	14.60	13.00
LCK-BTY0837-24PDLYR-GO	2*12	8.80	15.40	13.80
LCK-BTY0837-26PDLYR-GO	2*13	9.60	16.20	14.60
LCK-BTY0837-28PDLYR-GO	2*14	10.40	17.00	15.40
LCK-BTY0837-30PDLYR-GO	2*15	11.20	17.80	16.20
LCK-BTY0837-32PDLYR-GO	2*16	12.00	18.60	17.00
LCK-BTY0837-34PDLYR-GO	2*17	12.80	19.40	17.80
LCK-BTY0837-36PDLYR-GO	2*18	13.60	20.20	18.60
LCK-BTY0837-38PDLYR-GO	2*19	14.40	21.00	19.40
LCK-BTY0837-40PDLYR-GO	2*20	15.20	21.80	20.20
LCK-BTY0837-42PDLYR-GO	2*21	16.00	22.60	21.00
LCK-BTY0837-44PDLYR-GO	2*22	16.80	23.40	21.80
LCK-BTY0837-46PDLYR-GO	2*23	17.60	24.20	22.60
LCK-BTY0837-48PDLYR-GO	2*24	18.40	25.00	23.40
LCK-BTY0837-50PDLYR-GO	2*25	19.20	25.80	24.20
.....	...	...	...	...
LCK-BTY0837-200PDLYR-GO	2*100	79.20	85.80	84.20

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT




UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器 (深圳) 有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.8 Pitch B型立式BTB母座胶芯(单高3.7)
CHECKED		DATE			
APPROVED		DATE			
PART NO: LCK-BTY0837-XXPDLYR-GO				REV: 04	SCALE: 1:1
DRAWING NO: 102022802				UNIT: mm	
				SIZE: A4	SHEET: 1/1

RoHS Compliant



MEASURE POINT: (QP)
QUADRANT POINT (TP)
TANGENCY POINT (IP)
INTERSECTION POINT

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器 (深圳) 有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:			
CHECKED		DATE		0.8 Pitch B型立式BTB插座兼公座(单高3.7)			
APPROVED		DATE					
PART NO: LCK-BTY0837-XXPDLYR-GO				REV: 04	SCALE: 1:1	UNIT: mm	
DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1		