







RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

序号	品名	材质
①	0.8 Pitch双槽立式BTB母座胶芯	PA10T UL94 V-0, 颜色:黑色
②	0.8 Pitch双槽立式BTB母座端子	铜合金/表面点镀金
③	0.8 Pitch双槽立式BTB母座吸盖	LCP UL94 V-0, 颜色:黑色



High photosynthesis 公高(H)	The female seat height 母座半高(H1)	The male seat height 公座半高(H2)	Insertion height (H3)
4.0	3.0	1.0	1.9
4.5	3.5	1.0	1.9
5.0	3.0/4.0	2.0/1.0	1.9
5.5	3.5/4.5	2.0/1.0	1.9
6.0	4.0	2.0	1.9
6.5	4.5	2.0	1.9
7.0	3.0	4.0	1.9
7.5	3.5	4.0	1.9
8.0	4.0	4.0	1.9
8.5	4.5	4.0	1.9

Part No	CKT	A	B	C	D	E
LCK-BTY0835-8PSLYR-GO	8	2.40	3.50	5.10	4.20	4.00
LCK-BTY0835-10PSLYR-GO	10	3.20	4.30	5.90	5.00	
LCK-BTY0835-12PSLYR-GO	12	4.00	5.10	6.70	5.80	
LCK-BTY0835-14PSLYR-GO	14	4.80	5.90	7.50	6.60	
LCK-BTY0835-16PSLYR-GO	16	5.60	6.70	8.30	7.40	
LCK-BTY0835-18PSLYR-GO	18	6.40	7.50	9.10	8.20	
LCK-BTY0835-20PSLYR-GO	20	7.20	8.30	9.90	9.00	
LCK-BTY0835-22PSLYR-GO	22	8.00	9.10	10.70	9.80	
LCK-BTY0835-24PSLYR-GO	24	8.80	9.90	11.50	10.60	8.00
LCK-BTY0835-26PSLYR-GO	26	9.60	10.70	12.30	11.40	
LCK-BTY0835-28PSLYR-GO	28	10.40	11.50	13.10	12.20	
LCK-BTY0835-30PSLYR-GO	30	11.20	12.30	13.90	13.00	
LCK-BTY0835-32PSLYR-GO	32	12.00	13.10	14.70	13.80	
LCK-BTY0835-34PSLYR-GO	34	12.80	13.90	15.50	14.60	
LCK-BTY0835-36PSLYR-GO	36	13.6	14.70	16.30	15.40	
LCK-BTY0835-38PSLYR-GO	38	14.40	15.50	17.10	16.20	
LCK-BTY0835-40PSLYR-GO	40	15.20	16.30	17.90	17.00	
LCK-BTY0835-44PSLYR-GO	44	16.80	17.90	19.50	18.60	D
LCK-BTY0835-50PSLYR-GO	50	19.20	20.30	21.90	21.00	
LCK-BTY0835-60PSLYR-GO	60	23.20	24.30	25.90	25.00	
LCK-BTY0835-70PSLYR-GO	70	27.20	28.30	29.90	29.00	
LCK-BTY0835-80PSLYR-GO	80	31.20	32.30	33.90	33.00	
LCK-BTY0835-100PSLYR-GO	100	39.20	40.30	41.90	41.00	

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.8 Pitch双槽立式BTB母座业务图(单高3.5)		
CHECKED		DATE		REV:	04	SCALE:	1:1
APPROVED		DATE		UNIT:	mm		
PART NO:	LCK-BTY0835-XXPSLYR-GO			SIZE:	A4	SHEET:	1/1
DRAWING NO:	102022802						