







RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C} \sim 85^{\circ}\text{C}$ 。
3. 额定电压: 125V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。

台高(H)	公座单高	母座单高
3.0	2.2	2.2
3.5	2.2	2.7
4.0	2.2	3.2
5.0	2.6	4.4



序号	品名	材质
①	0.5 Pitch B型单槽立式 BTB母座底壳	LCP UL94 V-0 颜色: 米黄色
②	0.5 Pitch B型单槽立式 BTB母座端子	铜合金/表面镀锡/表面点镀金
③	0.5 Pitch B型单槽立式 BTB母座焊片	铜合金/表面镀锡

Part No	CKT	A	B	C	D	E
LCK-BTY0522-10PDLYC-GO	2X5	2.00	3.20	4.70	6.06	4.10
LCK-BTY0522-12PDLYC-GO	2X6	2.50	3.70	5.20	6.56	4.60
LCK-BTY0522-14PDLYC-GO	2X7	3.00	4.20	5.70	7.06	5.10
LCK-BTY0522-16PDLYC-GO	2X8	3.50	4.70	6.20	7.56	5.60
LCK-BTY0522-18PDLYC-GO	2X9	4.00	5.20	6.70	8.06	6.10
LCK-BTY0522-20PDLYC-GO	2X10	4.50	5.70	7.20	8.56	6.60
LCK-BTY0522-22PDLYC-GO	2X11	5.00	6.20	7.70	9.06	7.10
LCK-BTY0522-24PDLYC-GO	2X12	5.50	6.70	8.20	9.56	7.60
LCK-BTY0522-26PDLYC-GO	2X13	6.00	7.20	8.70	10.06	8.10
LCK-BTY0522-28PDLYC-GO	2X14	6.50	7.70	9.20	10.56	8.60
LCK-BTY0522-30PDLYC-GO	2X15	7.00	8.20	9.70	11.06	9.10
LCK-BTY0522-32PDLYC-GO	2X16	7.50	8.70	10.20	11.56	9.60
LCK-BTY0522-34PDLYC-GO	2X17	8.00	9.20	10.70	12.06	10.10
LCK-BTY0522-36PDLYC-GO	2X18	8.50	9.70	11.20	12.56	10.60
LCK-BTY0522-38PDLYC-GO	2X19	9.00	10.20	11.70	13.06	11.10
LCK-BTY0522-40PDLYC-GO	2X20	9.50	10.70	12.20	13.56	11.60
LCK-BTY0522-44PDLYC-GO	2X22	10.50	11.70	13.20	14.56	12.60
LCK-BTY0522-50PDLYC-GO	2X25	12.00	13.20	14.70	16.06	14.10
LCK-BTY0522-60PDLYC-GO	2X30	14.50	15.70	17.20	18.56	16.60
LCK-BTY0522-70PDLYC-GO	2X35	17.00	18.20	19.70	21.06	19.10
LCK-BTY0522-80PDLYC-GO	2X40	19.50	20.70	22.20	23.56	21.60

MEASURE POINT:
QUADRANT POINT (QP)
TANGENCY POINT (TP)
INTERSECTION POINT (IP)

UNLESS OTHERWISE SPECIFIED, TOLERANCE:
X. ± 0.25
X.x ± 0.20
X.xx ± 0.15
ANGULAR $\pm 3^{\circ}$

联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.5 Pitch B型单槽立式BTB母座业务图 (单高2.2)		
CHECKED		DATE					
APPROVED		DATE					
PART NO:	LCK-BTY0522-XXPDLYC-GO			REV:	04	SCALE:	1:1
DRAWING NO:	102022802			SIZE:	A4	SHEET:	1/1