


RoHS Compliant



SPECIFICATION:

1.MATERIAL:

- 1.1 HOUSING: LCP UL 94V-0
- 1.2 COLOR: BLACK
- 1.3 CONTACT: BRASS C2680-H, T=0.25mm
- 1.4 PEG: BRASS C2680R-H, T=0.30mm

2.FINISH:

- 2.1 CONTACT: 1u"/3u"/5u"/15u" GOLD/TIN PLATING ON CONTACT AREA
- 2.2 100u" TIN PLATING ON SOLDER TAILS
- 2.3 50u" NICKEL UNDERPLATING OVERALL
- 2.4 PEG: 100u" TIN PLATING ON SOLDER TAILS
- 2.5 50u" NICKEL UNDERPLATING OVERALL

环境要求		产品必须符合ROHS要求						
3	Peg	Brass C2680R-H		Tin/Ni Plated				
2	Terminal	Brass C2680R-H		Gold/Tin Plated				
1	Housing	High Temp	Black	UL 94V-0				
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK				
MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT	(QP)							
TANGENCY POINT	(TP)							
INTERSECTION POINT	(IP)							
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X.	±0.25	CHECKED		DATE		SATA 7P 公座 三面包SMT型(半包开槽)		
X.x	±0.20	APPROVED		DATE				
X.xx	±0.15	PART NO: LCK-STA-03M07P-BG0				REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR	±3°	DRAWING NO: 102022802				SIZE: A4	SHEET: 1/1	