


RoHS Compliant



SPECIFICATION:

1 MATERIAL:

- 1.1 HOUSING: LCP 30% G/F UL 94V-0
- 1.2 COLOR: BLACK
- 1.3 CONTACT: PHOSPHOR BRONZE C2680 H,T=0.25mm
- 1.4 PEG: BRASS C2680R H,T=0.30mm
- 1.5 SHELL: spcc,T=0.30mm

2 FINISH:

- 2.1 CONTACT: G/F GOLD/TIN PLATING ON CONTACT AREA
- 2.2 100u" MIN. Matte TIN PLATING ON SOLDER TAILS
- 2.3 50u" MIN. NICKEL UNDERPLATING OVERALL
- 3 PEG: 100u" MIN. Matte TIN PLATING ON SOLDER TAILS
- 3.1 50u" MIN. NICKEL UNDERPLATING OVERALL
- 4 SHELL: 100u" MIN. Matte TIN PLATING ON SOLDER TAILS
- 4.1 50u" MIN. NICKEL UNDERPLATING OVERALL

MEASURE POINT:

QUADRANT POINT

QP

TANGENCY POINT

TP

INTERSECTION POINT

IP

UNLESS OTHERWISE SPECIFIED, TOLERANCE:

X. ± 0.25

X.x ± 0.20

X.xx ± 0.15

ANGULAR $\pm 3^\circ$

联晟欣连接器 (深圳) 有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	SATA 7Pin 公座 90°AB 型双柱铁壳成品客户图
CHECKED		DATE			
APPROVED		DATE			
PART NO:	LCK-STA-04M07P-BG0	REV:	04	SCALE:	1:1
DRAWING NO:	102022802	SIZE:	A4	SHEET:	1/1