


RoHS Compliant



SPECIFICATION:

1.MATERIAL:

1.1 HOUSING:LCP 30% G/F UL 94V-0

1.2 COLOR:BLACK

1.3 CONTACT:BRASS C2680R-H,T=0.25mm

2.FINISH:

2.1 CONTACT:1u",3u",5u",15u"30u"GOLD PLATING ON CONTACT AREA

2.2 100u" MIN.TIN PLATING ON SOLDER TAILS

2.3 40u" MIN.NICKEL UNDERPLATING OVER ALL

3.ELECTRICAL:



3.1 CURRENT RATING:1.5 AMPERE PER CONTACT

3.2 CONTACT RESISTANCE:30 MILLIOHMS MAX

3.3 INSULATION RESISTANCE:1000 MEGOHMS MIN

3.4 DIELECTRIC WITH STANDING VOLTAGE:500 VDC

3.5 OPERATING TEMPERATURE: -40°C ~ +85°C



环境要求		产品必须符合ROHS要求		
2	Terminal	BRASS C2680R-H	Gold/Tin Plated	
1	Housing	High Temp	Black	UL 94V-0
NO.	DESCRIPTION	MATERIAL	COLOR	REMARK
MEASURE POINT: QUADRANT POINT (QP) TANGENCY POINT (TP) INTERSECTION POINT (IP)		联晟欣连接器(深圳)有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd		
UNLESS OTHERWISE SPECIFIED,TOLERANCE:		DESIGN	Andy	DATE
X.		CHECKED		DATE
X.x		APPROVED		DATE
X.xx		PART NO:	LCK-STA-013M22P-BG0	REV: 04
ANGULAR		DRAWING NO:	102022802	SCALE: 1:1
		UNIT: mm		
		SHEET: 1/1		