








Technical drawing of a rectangular container. The drawing shows a top view of the container with a series of vertical lines along the top edge, possibly representing a lid or a series of compartments. The dimensions are given as 38.05 ± 0.25 and 40.43 ± 0.25 . A detail callout labeled (1) points to a specific feature on the right side of the container.



SECTION A-A



SECTION B-B

ITEM	DIM A	形状	DIM B
SATA-10M-22AWB-C21	2.10		2.08
SATA-10M-22AWB-C23	2.30		

1.MATERIAL:

1.1 HOUSING: LCP UL 94V-0

1.2 COLOR: BLACK

1.3 CONTACT: PHOSPHOR BRONZE C5191R-H, T=0.25mm

1.4 PEG: BRASS C2680R-H, T=0.30mm

2.FINISH:


2.1 CONTACT: 1u"/3u"/5u"/15u" GOLD PLATING ON CONTACT AREA

2.2 100u" TIN PLATING ON SOLDERTAILS

2.3 30u" NICKEL UNDERPLATING OVER ALL

2.4 PEG:100u" TIN PLATING ON SOLDERTAILS

2.5 30u" NICKEL UNDERPLATING OVER ALL



环保要求		产品必须符合ROHS要求						
3	Peg	Brass C2680R-H			Tin/Ni Plated			
2	Terminal	Pho.Bronze C5191R-H			Gold/Tin Plated			
1	Housing	High Temp		Black	UL 94V-0			
NO.	DESCRIPTION	MATERIAL		COLOR	REMARK			
MEASURE POINT:		 联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd						
QUADRANT POINT (QP)								
TANGENCY POINT (TP)								
INTERSECTION POINT (IP)								
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN	Andy	DATE	2014.12.24	TITLE:		
X. ±0.25		CHECKED		DATE		SATA 7+15P 母座板下5.0 SMT 侧插式		
X.x ±0.20		APPROVED		DATE				
X.xx ±0.15		PART NO: LCK-ST A-016F2P-BG0						
ANGULAR ±3°		DRAWING NO: 102022802				REV: 04	SCALE: 1:1	UNIT: mm
						SHEET: 1/1	 	