






RoHS Compliant



Part No	CKT	A	B	C
LCK-BTG0857-20PDLYR-GO	2*10	7.20	13.80	12.20
LCK-BTG0857-22PDLYR-GO	2*11	8.00	14.60	13.00
LCK-BTG0857-24PDLYR-GO	2*12	8.80	15.40	13.80
LCK-BTG0857-26PDLYR-GO	2*13	9.60	16.20	14.60
LCK-BTG0857-28PDLYR-GO	2*14	10.40	17.00	15.40
LCK-BTG0857-30PDLYR-GO	2*15	11.20	17.80	16.20
LCK-BTG0857-32PDLYR-GO	2*16	12.00	18.60	17.00
LCK-BTG0857-34PDLYR-GO	2*17	12.80	19.40	17.80
LCK-BTG0857-36PDLYR-GO	2*18	13.60	20.20	18.60
LCK-BTG0857-38PDLYR-GO	2*19	14.40	21.00	19.40
LCK-BTG0857-40PDLYR-GO	2*20	15.20	21.80	20.20
LCK-BTG0857-42PDLYR-GO	2*21	16.00	22.60	21.00
LCK-BTG0857-44PDLYR-GO	2*22	16.80	23.40	21.80
LCK-BTG0857-46PDLYR-GO	2*23	17.60	24.20	22.60
LCK-BTG0857-48PDLYR-GO	2*24	18.40	25.00	23.40
LCK-BTG0857-50PDLYR-GO	2*25	19.20	25.80	24.20
.....	...	...	...	...
LCK-BTG0857-200PDLYR-GO	2*100	79.20	85.80	84.20


技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: -40°C~85°C.
3. 额定电压: 100V, AC.
4. 接触电阻: $\leq 0.05\Omega$.
5. 绝缘电阻: $\geq 500M\Omega$

序号	品名	材质
①	0.8 Pitch B型立式 BTB公座胶芯	LCP UL94 V-0, 颜色: 本色
②	0.8 Pitch B型立式 BTB公座端子	铜合金/表面点镀金
③	0.8 Pitch B型立式 BTB公座吸盘	不锈钢

MEASURE POINT:	QUADRANT POINT	TANGENCY POINT	INTERSECTION POINT
UNLESS OTHERWISE SPECIFIED, TOLERANCE:	X. ±0.25	X.x ±0.20	X.xx ±0.15
ANGULAR	±3°		

联晟欣连接器 (深圳) 有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
DESIGN	Andy	DATE	2014.12.24
CHECKED		DATE	
APPROVED		DATE	
PART NO: LCK-BTG0857-XXPDLYR-GO		REV: 04	SCALE: 1:1
DRAWING NO: 102022802		SIZE: A4	SHEET: 1/1



MEASURE POINT: QUADRANT POINT TANGENCY POINT INTERSECTION POINT		QP TP IP	联晟欣连接器（深圳）有限公司 Lianshengxin Connector (Shenzhen) Co., Ltd			
UNLESS OTHERWISE SPECIFIED, TOLERANCE:		DESIGN Andy		DATE 2014.12.24	TITLE: 0.8 Pitch B型立式BTB公座业务图(单高5.7)	
X. ±0.25		CHECKED		DATE		
X.x ±0.20		APPROVED		DATE		
X.xx ±0.15		PART NO: LCK-BTG0857-XXPDLYR-GO		REV: 04	SCALE: 1:1	UNIT: mm
ANGULAR ±3°		DRAWING NO:		SIZE: A4	SHEET: 1/1	