







RoHS Compliant



技术指标:

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。
2. 温度范围: $-40^{\circ}\text{C}\sim 85^{\circ}\text{C}$ 。
3. 额定电压: 50V, AC。
4. 接触电阻: $\leq 0.02\Omega$ 。
5. 绝缘电阻: $\geq 100\text{M}\Omega$ 。



合高(H)	公座单高	母座单高
1.5	1.3	1.4
2.0	1.3	1.9
2.5	1.3	2.4

序号	品名	材质
①	0.5 Pitch C型 单槽立式BTB母座胶芯	LCP UL94 V-0 颜色:米黄色
②	0.5 Pitch C型 单槽立式BTB母座端子	铜合金/表面点镀金

Part No	CKT	A	B	C
LCK-BTY0519-10PDLWR-GO	2X5	2.00	3.40	5.50
LCK-BTY0519-12PDLWR-GO	2X6	2.50	3.90	6.00
LCK-BTY0519-14PDLWR-GO	2X7	3.00	4.40	6.50
LCK-BTY0519-16PDLWR-GO	2X8	3.50	4.90	7.00
LCK-BTY0519-18PDLWR-GO	2X9	4.00	5.40	7.50
LCK-BTY0519-20PDLWR-GO	2X10	4.50	5.90	8.00
LCK-BTY0519-22PDLWR-GO	2X11	5.00	6.40	8.50
LCK-BTY0519-24PDLWR-GO	2X12	5.50	6.90	9.00
LCK-BTY0519-26PDLWR-GO	2X13	6.00	7.40	9.50
LCK-BTY0519-28PDLWR-GO	2X14	6.50	7.90	10.00
LCK-BTY0519-30PDLWR-GO	2X15	7.00	8.40	10.50
LCK-BTY0519-32PDLWR-GO	2X16	7.50	8.90	11.00
LCK-BTY0519-34PDLWR-GO	2X17	8.00	9.40	11.50
LCK-BTY0519-36PDLWR-GO	2X18	8.50	9.90	12.00
LCK-BTY0519-38PDLWR-GO	2X19	9.00	10.40	12.50
LCK-BTY0519-40PDLWR-GO	2X20	9.50	10.90	13.00
.....	...	...	...	...
LCK-BTY0519-100PDLWR-GO	2X50	24.50	25.90	28.00

MEASURE POINT:
QUADRANT POINT
TANGENCY POINT
INTERSECTION POINT



UNLESS OTHERWISE
SPECIFIED, TOLERANCE:
X. ±0.25
X.x ±0.20
X.xx ±0.15
ANGULAR ±3°



联晟欣连接器(深圳)有限公司
Lianshengxin Connector (Shenzhen) Co., Ltd

DESIGN	Andy	DATE	2014.12.24	TITLE:	0.5 Pitch C型单槽立式BTB母座业务图(单高1.9)
CHECKED		DATE			
APPROVED		DATE			
PART NO: LCK-BTY0519-XXPDLWR-GO				REV: 04	SCALE: 1:1
DRAWING NO: 102022802				UNIT: mm	
				SIZE: A4	SHEET: 1/1