




P.C.B Layout

一. 电气性能:

1-1. 额定电流: 3A AC DC.

1-2. 接触电阻: $\leq 20\text{m}\Omega$

1-3. 绝缘电阻: $\geq 1000\text{M}\Omega$ Min

1-4. 耐压: 550V AC/Minute

二. 物理特性:

2-1. 操作温度: $-55^{\circ}\text{C} \sim 105^{\circ}\text{C}$

2-2. 焊接温度: $+220^{\circ}\text{C}$, 10s max

三. 材质:

3-1. 塑胶: PBT(Black) UL94V-0

3-2. 插针: Brass/Gold plated

PIN	A	AI	B
3	15.24	12.94	5.08
4	17.78	15.48	7.62
5	20.32	18.02	10.16
6	22.86	20.56	12.70
7	25.40	23.10	15.24
8	27.94	25.64	17.78
9	30.48	28.18	20.32
10	33.02	30.72	22.86
11	35.56	33.26	25.40
12	38.10	35.80	27.94
13	40.64	38.34	30.48
14	43.18	40.88	33.02
15	45.72	43.42	35.56
16	48.26	45.96	38.10
17	50.80	48.50	40.64
18	53.34	51.04	43.18
19	55.88	53.58	45.72
20	58.42	56.12	48.26
21	60.96	58.66	50.80
22	63.50	61.20	53.34
23	66.04	63.74	55.88
24	68.58	66.28	58.42
25	71.12	68.82	60.96
26	73.66	71.36	63.50
27	76.20	73.90	66.04
28	78.74	76.44	68.58
29	81.28	78.98	71.12
30	83.82	81.52	73.66

浙江博穆电子精密有限公司

图名: 2.54-2xNA

图号: XXXXXXXXXXXXXXXXXXXX

未标注公差

XX.	± 0.40	XX.°	$\pm 2^{\circ}$
X.	± 0.30	.XX°	$\pm 1^{\circ}$
.X	± 0.20		
.XX	± 0.15		

绘制:

韩金锋

单位:

MM

签发:

比例:

1:1

审核:

视图:

