







REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

PART NO	PIN	A	B
C-JC2.5-1-W2P62	2	2.50	5.5
C-JC2.5-1-W3P62	3	5.00	8.0
C-JC2.5-1-W4P62	4	7.50	10.5
C-JC2.5-1-W5P62	5	10.00	13.0
C-JC2.5-1-W6P62	6	12.50	15.5
C-JC2.5-1-W7P62	7	15.00	18.0
C-JC2.5-1-W8P62	8	17.50	20.5
C-JC2.5-1-W9P62	9	20.00	23.0
C-JC2.5-1-W10P62	10	22.50	25.5
C-JC2.5-1-W11P62	11	25.00	28.0
C-JC2.5-1-W12P62	12	27.50	30.5
C-JC2.5-1-W13P62	13	30.00	33.0
C-JC2.5-1-W14P62	14	32.50	35.5
C-JC2.5-1-W15P62	15	35.00	38.0
C-JC2.5-1-W16P62	16	37.50	40.5

技术指标(Technical Index):

- 1.温度范围(Temperature range): $-25^{\circ}\text{C}\sim+85^{\circ}\text{C}$.
- 2.额定电压(Rated voltage):250V AC,DC.
- 3.耐电压(Withstanding Voltage):1000V AC/minute.
- 4.接触电阻(Contact resistance): $\leq 20\text{m}\Omega$.
- 5.绝缘电阻(Insulation resistance): $\geq 1000\text{M}\Omega$.
- 6.额定电流(Rated Current): 2.5A AC,DC.

材料:

- 1.塑胶:PA66 白色

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X. ± 0.50	$\pm 1^{\circ}$	PART NO.	TITLE:		
X.X ± 0.20		C-JC2.5-1-WNP62	JC25 WTB等插板胶芯		
X.XX ± 0.10		DESIGN: Ethan	MANUFACTURE DWG		
UNITS	mm	CHED: Olvia		SCALE	SHEET
MATERILA	---	APPD: Ava		N:A	1/1